

Lift lever chain hoist PT - multi-purpose device

Refined technology and improved look

Yale

Application:

For everyday use under the most difficult conditions. Suitable for load securing in accordance with EN 12195.

Execution:

- Proven sheet steel housing
- Short hand lever with rubber handle for safe operation of the device
- With standard chain release for quick attachment of the load or passage of the load chain in both directions
- Zinc-plated or additionally yellow chromated round steel chain in accordance with all valid national and international regulations
- Swivel-mounted, forged hooks made of age-resistant heat-treated steel, with safety brackets

Advantage:

- Extremely low weight
- With standard chain release



Art. no.	77157 104
Brand	YALE
Manufacturer Part Number	N02200008
Model	PT 6300
Load-carrying capacity	6300 kg
Nominal chain thickness	27.2 mm
Chain diameter	9 mm
Stroke force at nominal load	39 daN
Length of lever	370 mm
Stroke height per lever revolution	8 mm
Weight at normal stroke	31 kg
Min. hook spacing	580 mm
Number of load chains	2 PCS
Hook width	43 mm
Width of mouth	46 mm
Hook thickness	53 mm
Housing length	259 mm
Material of hook	Steel
Material of housing	Steel plate
Material of handle	Rubber
Housing length 2	174 mm
Radius of the hook	85 mm
Device depth	185 mm
Depth to tip of the hook 2	102 mm
Depth to tip of the hook 1	185 mm
EN standard	12195-3
Gross Weight	31.000 kg
Product Group	7EE

EAN

4025092076494