


# DURACELL®

# CR2032

Lithium/Manganese Dioxide Battery

Li/MnO<sub>2</sub>



## SPECIFICATIONS

**Nominal Voltage:** 3.0 V

**Typical Voltage:** 3.1 – 3.3 V

**Rated Capacity:** 210 mAh on  
15 k $\Omega$  to 2.0 V

**Average Weight:** 3.2 g (0.113 oz.)


**Terminals:** Flat

**Operating Temp. Range:** -20°C to 60°C  
(-4°F to 140°F)


**NEDA/ANSI:** 5004LC

**IEC:** CR2032

## Discharge Characteristics



## Temperature Characteristics




# DURACELL®

BATTERIES


Berkshire Corporate Park  
Bethel, CT. 06801 U.S.A.  
Telephone: Toll-free 1-800-544-5454  
www.duracell.com

Delivered capacity is dependent on the applied load, operating temperature and cut-off voltage. Please refer to the charts and discharge data shown for examples of the energy/service life that the battery will provide for various load conditions.


### Load vs. Operating Voltage




### Load vs. Capacity



### Pulse Discharge Characteristics



### Storage Characteristics



# DURACELL®

BATTERIES

Berkshire Corporate Park  
Bethel, CT. 06801 U.S.A.  
Telephone: Toll-free 1-800-544-5454  
www.duracell.com

Delivered capacity is dependent on the applied load, operating temperature and cut-off voltage. Please refer to the charts and discharge data shown for examples of the energy/service life that the battery will provide for various load conditions.