LM4861 1.1W Audio Power Amplifier with Shutdown Mode



Literature Number: SNAS095B

1.0% (max)



## LM4861 Boomer® Audio Power Amplifier Series 1.1W Audio Power Amplifier with Shutdown Mode **Key Specifications General Description**

The LM4861 is a bridge-connected audio power amplifier capable of delivering 1.1W of continuous average power to an 8 $\Omega$  load with 1% THD+N using a 5V power supply.

Boomer audio power amplifiers were designed specifically to provide high quality output power with a minimal amount of external components using surface mount packaging. Since the LM4861 does not require output coupling capacitors, bootstrap capacitors, or snubber networks, it is optimally suited for low-power portable systems.

The LM4861 features an externally controlled, low-power consumption shutdown mode, as well as an internal thermal shutdown protection mechanism.

The unity-gain stable LM4861 can be configured by external gain-setting resistors for differential gains of up to 10 without the use of external compensation components. Higher gains may be achieved with suitable compensation.

- THD+N for 1kHz at 1W continuous average output power into  $8\Omega$
- Output power at 10% THD+N 1.5W (typ) at 1kHz into  $8\Omega$
- Shutdown Current 0.6µA (typ)


## Features

- No output coupling capacitors, bootstrap capacitors, or snubber circuits are necessary
- Small Outline (SO) packaging
- Compatible with PC power supplies
- Thermal shutdown protection circuitry
- Unity-gain stable
- External gain configuration capability

## Applications


- Personal computers
- Portable consumer products
- Self-powered speakers
- Toys and games

## **Connection Diagram**



Top View Order Number LM4861M See NS Package Number M08A

Boomer® is a registered trademark of National Semiconductor Corporation.



## Absolute Maximum Ratings (Note 2)

If Military/Aerospace specified devices are required, please contact the National Semiconductor Sales Office/ Distributors for availability and specifications.

Supply Voltage	6.0V
Storage Temperature	–65°C to +150°C
Input Voltage	–0.3V to V <sub>DD</sub> + 0.3V
Power Dissipation (Note 3)	Internally limited
ESD Susceptibility (Note 4)	3000V
ESD Susceptibility (Note 5)	250V
Junction Temperature	150°C
Soldering Information	
Small Outline Package	
Vapor Phase (60 sec.)	215°C
Infrared (15 sec.)	220°C

See AN-450 *"Surface Mounting and their Effects on Product Reliability"* for other methods of soldering surface mount devices.

## **Operating Ratings**

Temperature Range	
$T_{MIN} \le T_A \le T_{MAX}$	$-40^{\circ}C \le T_A \le$
	+85°C
Supply Voltage	$2.0V \leq V_{DD} \leq 5.5V$
Thermal Resistance	
$\theta_{\rm JC}$ (typ)—M08A	35°C/W
$\theta_{JA}$ (typ)—M08A	140°C/W
$\theta_{\rm JC}$ (typ)—N08E	37°C/W
θ <sub>JA</sub> (typ)—N08E	107°C/W

### Electrical Characteristics (Note 1) (Note 2)

The following specifications apply for  $V_{DD}$  = 5V, unless otherwise specified. Limits apply for  $T_A$  = 25°C.

			LM4861			
Symbol	Parameter	Conditions	Typical	Limit	Units (Limits)	
			(Note 6)	(Note 7)	(Linits)	
V <sub>DD</sub>	Supply Voltage			2.0	V (min)	
				5.5	V (max)	
I <sub>DD</sub>	Quiescent Power Supply Current	$V_{IN} = 0V, I_{O} = 0A$ (Note 8)	6.5	10.0	mA (max)	
I <sub>SD</sub>	Shutdown Current	$V_{pin1} = V_{DD}$	0.6	10.0	μA (max)	
V <sub>os</sub>	Output Offset Voltage	V <sub>IN</sub> = 0V	5.0	50.0	mV (max)	
Po	Output Power	THD = 1% (max); f = 1 kHz	1.1	1.0	W (min)	
THD+N	Total Harmonic Distortion + Noise	$P_{O} = 1Wrms; 20 Hz \le f \le 20 kHz$	0.72		%	
PSRR	Power Supply Rejection Ratio	$V_{DD} = 4.9V$ to 5.1V	65		dB	

Note 1: All voltages are measured with respect to the ground pin, unless otherwise specified.

**Note 2:** Absolute Maximum Ratings indicate limits beyond which damage to the device may occur. Operating Ratings indicate conditions for which the device is functional, but do not guarantee specific performance limits. Electrical Characteristics state DC and AC electrical specifications under particular test conditions which guarantee specific performance limits. This assumes that the device is within the Operating Ratings. Specifications are not guaranteed for parameters where no limit is given, however, the typical value is a good indication of device performance.

**Note 3:** The maximum power dissipation must be derated at elevated temperatures and is dictated by  $T_{JMAX}$ ,  $\theta_{JA}$ , and the ambient temperature  $T_A$ . The maximum allowable power dissipation is  $P_{DMAX} = (T_{JMAX} - T_A)/\theta_{JA}$  or the number given in the Absolute Maximum Ratings, whichever is lower. For the LM4861,  $T_{JMAX} = 150^{\circ}$ C, and the typical junction-to-ambient thermal resistance, when board mounted, is 140°C/W.


Note 4: Human body model, 100pF discharged through a  $1.5 k\Omega$  resistor.

Note 5: Machine Model, 220pF-240pF discharged through all pins.

Note 6: Typicals are measured at  $25^{\circ}C$  and represent the parametric norm.

Note 7: Limits are guaranteed to Nationai's AOQL (Average Outgoing Quality Level).

Note 8: The quiescent power supply current depends on the offset voltage when a practical load is connected to the amplifier.




## **External Components Description**


(Figures 1, 2)


Components	Functional Description			
1. R <sub>i</sub>	Inverting input resistance which sets the closed-loop gain in conjunction with R <sub>f</sub> . This resistor also forms			
	a high pass filter with $C_i$ at $f_c = 1 / (2\pi R_i C_i)$ .			
2. C <sub>i</sub>	Input coupling capacitor which blocks DC voltage at the amplifier's input terminals. Also creates a			
	highpass filter with $R_i$ at $f_c = 1 / (2\pi R_i C_i)$ .			
3. R <sub>f</sub>	Feedback resistance which sets closed-loop gain in conjunction with R <sub>i</sub> .			
4. C <sub>S</sub>	Supply bypass capacitor which provides power supply filtering. Refer to the <b>Application Information</b> section for proper placement and selection of supply bypass capacitor.			
5. C <sub>B</sub>	Bypass pin capacitor which provides half supply filtering. Refer to the Application Information section			
	for proper placement and selection of bypass capacitor.			
6. C <sub>f</sub> (Note 9)	$C_f$ in conjunction with $R_f$ creates a low-pass filter which bandwidth limits the amplifier and prevents possible high frequency oscillation bursts. $f_c = 1 / (2\pi R_f C_f)$			

Note 9: Optional component dependent upon specific design requirements. Refer to the Application Information section for more information.


## **Typical Performance Characteristics**









THD+N vs Output Power







## Application Information

#### **BRIDGE CONFIGURATION EXPLANATION**

As shown in *Figure 1*, the LM4861 has two operational amplifiers internally, allowing for a few different amplifier configurations. The first amplifier's gain is externally configurable, while the second amplifier is internally fixed in a unity-gain, inverting configuration. The closed-loop gain of the first amplifier is set by selecting the ratio of R<sub>f</sub> to R<sub>i</sub> while the second amplifier's gain is fixed by the two internal 40k $\Omega$  resistors. *Figure 1* shows that the output of amplifier one serves as the input to amplifier two which results in both amplifiers producing signals identical in magnitude, but out of phase 180°. Consequently, the differential gain for the IC is:

#### $A_{vd} = 2 * (R_f / R_i)$

By driving the load differentially through outputs  $V_{O1}$  and  $V_{O2}$ , an amplifier configuration commonly referred to as "bridged mode" is established. Bridged mode operation is different from the classical single-ended amplifier configuration where one side of its load is connected to ground.

A bridge amplifier design has a few distinct advantages over the single-ended configuration, as it provides differential drive to the load, thus doubling output swing for a specified supply voltage. Consequently, four times the output power is possible as compared to a single-ended amplifier under the same conditions. This increase in attainable output power assumes that the amplifier is not current limited or clipped. In order to choose an amplifier's closed-loop gain without causing excessive clipping which will damage high frequency transducers used in loudspeaker systems, please refer to the **Audio Power Amplifier Design** section.

A bridge configuration, such as the one used in Boomer Audio Power Amplifiers, also creates a second advantage over single-ended amplifiers. Since the differential outputs, V<sub>O1</sub> and V<sub>O2</sub>, are biased at half-supply, no net DC voltage exists across the load. This eliminates the need for an output coupling capacitor which is required in a single supply, single-ended amplifier configuration. Without an output coupling capacitor in a single supply, single-ended amplifier, the half-supply bias across the load would result in both increased internal IC power dissipation and also permanent loudspeaker damage. An output coupling capacitor forms a high pass filter with the load requiring that a large value such as 470 $\mu$ F be used with an 8 $\Omega$  load to preserve low frequency response. This combination does not produce a flat response down to 20Hz, but does offer a compromise between printed circuit board size and system cost, versus low frequency response.

#### POWER DISSIPATION

Power dissipation is a major concern when designing a successful amplifier, whether the amplifier is bridged or single-ended. A direct consequence of the increased power delivered to the load by a bridge amplifier is an increase in internal power dissipation. Equation 1 states the maximum power dissipation point for a bridge amplifier operating at a given supply voltage and driving a specified output load.

$$P_{\rm DMAX} = 4^* (V_{\rm DD})^2 / (2\pi^2 R_{\rm L})$$
(1)

Since the LM4861 has two operational amplifiers in one package, the maximum internal power dissipation is 4 times that of a single-ended amplifier. Even with this substantial increase in power dissipation, the LM4861 does not require heatsinking. From Equation 1, assuming a 5V power supply and an  $8\Omega$  load, the maximum power dissipation point is

625mW.The maximum power dissipation point obtained from Equation 1 must not be greater than the power dissipation that results from Equation 2:

$$P_{DMAX} = (T_{JMAX} - T_A) / \theta_{JA}$$
(2)

For the LM4861 surface mount package,  $\theta_{JA} = 140^{\circ}$ C/W and  $T_{JMAX} = 150$ °C. Depending on the ambient temperature,  $T_A$ , of the system surroundings, Equation 2 can be used to find the maximum internal power dissipation supported by the IC packaging. If the result of Equation 1 is greater than that of Equation 2, then either the supply voltage must be decreased or the load impedance increased. For the typical application of a 5V power supply, with an  $8\Omega$  load, the maximum ambient temperature possible without violating the maximum junction temperature is approximately 62.5°C provided that device operation is around the maximum power dissipation point. Power dissipation is a function of output power and thus, if typical operation is not around the maximum power dissipation point, the ambient temperature can be increased. Refer to the Typical Performance Characteristics curves for power dissipation information for lower output powers.

#### POWER SUPPLY BYPASSING

As with any power amplifier, proper supply bypassing is critical for low noise performance and high power supply rejection. The capacitor location on both the bypass and power supply pins should be as close to the device as possible. As displayed in the **Typical Performance Characteristics** section, the effect of a larger half supply bypass capacitor is improved low frequency THD+N due to increased half-supply stability. Typical applications employ a 5V regulator with  $10\mu$ F and a  $0.1\mu$ F bypass capacitors which aid in supply stability, but do not eliminate the need for bypassing the supply nodes of the LM4861. The selection of bypass capacitors, especially C<sub>B</sub>, is thus dependant upon desired low frequency THD+N, system cost, and size constraints.

#### SHUTDOWN FUNCTION

In order to reduce power consumption while not in use, the LM4861 contains a shutdown pin to externally turn off the amplifier's bias circuitry. The shutdown feature turns the amplifier off when a logic high is placed on the shutdown pin. Upon going into shutdown, the output is immediately disconnected from the speaker. A typical quiescent current of 0.6µA results when the supply voltage is applied to the shutdown pin. In many applications, a microcontroller or microprocessor output is used to control the shutdown circuitry which provides a quick, smooth transition into shutdown. Another solution is to use a single-pole, single-throw switch that when closed, is connected to ground and enables the amplifier. If the switch is open, then a soft pull-up resistor of  $47k\Omega$  will disable the LM4861. There are no soft pull-down resistors inside the LM4861, so a definite shutdown pin voltage must be applied externally, or the internal logic gate will be left floating which could disable the amplifier unexpectedly.

#### HIGHER GAIN AUDIO AMPLIFIER

The LM4861 is unity-gain stable and requires no external components besides gain-setting resistors, an input coupling capacitor, and proper supply bypassing in the typical application. However, if a closed-loop differential gain of greater than 10 is required, a feedback capacitor may be needed, as shown in *Figure 2*, to bandwidth limit the amplifier. This feedback capacitor creates a low pass filter that eliminates

(3)

## Application Information (Continued)

possible high frequency oscillations. Care should be taken when calculating the –3dB frequency in that an incorrect combination of R<sub>f</sub> and C<sub>f</sub> will cause rolloff before 20kHz. A typical combination of feedback resistor and capacitor that will not produce audio band high frequency rolloff is R<sub>f</sub> = 100k $\Omega$  and C<sub>f</sub> = 5pF. These components result in a –3dB point of approximately 320kHz. Once the differential gain of the amplifier has been calculated, a choice of R<sub>f</sub> will result, and C<sub>f</sub> can then be calculated from the formula stated in the **External Components Description** section.

#### **VOICE-BAND AUDIO AMPLIFIER**

Many applications, such as telephony, only require a voiceband frequency response. Such an application usually requires a flat frequency response from 300Hz to 3.5kHz. By adjusting the component values of *Figure 2*, this common application requirement can be implemented. The combination of R<sub>i</sub> and C<sub>i</sub> form a highpass filter while R<sub>f</sub> and C<sub>f</sub> form a lowpass filter. Using the typical voice-band frequency range, with a passband differential gain of approximately 100, the following values of R<sub>i</sub>, C<sub>i</sub>, R<sub>f</sub>, and C<sub>f</sub> follow from the equations stated in the **External Components Description** section.

$$R_i$$
 = 10k $\Omega,~R_f$  = 510k ,C\_i = 0.22 \mu F, and C\_f = 15 pF

Five times away from a –3dB point is 0.17dB down from the flatband response. With this selection of components, the resulting –3dB points,  $f_L$  and  $f_H$ , are 72Hz and 20kHz, respectively, resulting in a flatband frequency response of better than ±0.25dB with a rolloff of 6dB/octave outside of the passband. If a steeper rolloff is required, other common bandpass filtering techniques can be used to achieve higher order filters.

#### SINGLE-ENDED AUDIO AMPLIFIER

Although the typical application for the LM4861 is a bridged monoaural amp, it can also be used to drive a load singleendedly in applications, such as PC cards, which require that one side of the load is tied to ground. Figure 3 shows a common single-ended application, where  $V_{O1}$  is used to drive the speaker. This output is coupled through a 470µF capacitor, which blocks the half-supply DC bias that exists in all single-supply amplifier configurations. This capacitor, designated  $C_O$  in Figure 3, in conjunction with  $R_L$ , forms a highpass filter. The -3dB point of this high pass filter is  $1/(2\pi R_1 C_0)$ , so care should be taken to make sure that the product of R<sub>1</sub> and C<sub>0</sub> is large enough to pass low frequencies to the load. When driving an  $8\Omega$  load, and if a full audio spectrum reproduction is required,  $\mathrm{C}_{\mathrm{O}}$  should be at least  $470\mu$ F. V<sub>O2</sub>, the output that is not used, is connected through a 0.1  $\mu$ F capacitor to a 2k $\Omega$  load to prevent instability. While such an instability will not affect the waveform of  $V_{O1}$ , it is good design practice to load the second output.

## AUDIO POWER AMPLIFIER DESIGN Design a 1W / $8\Omega$ Audio Amplifier

1 Wrms
8Ω
1 Vrms
20 kΩ
100 Hz–20 kHz ± 0.25 dB

A designer must first determine the needed supply rail to obtain the specified output power. By extrapolating from the Output Power vs Supply Voltage graph in the **Typical Performance Characteristics** section, the supply rail can be easily found. A second way to determine the minimum supply rail is to calculate the required V<sub>opeak</sub> using Equation 3 and add the dropout voltage. Using this method, the minimum supply voltage would be (V<sub>opeak</sub> + V<sub>OD</sub>, where V<sub>OD</sub> is typically 0.6V.

$$V_{opeak} = \sqrt{(2R_LP_0)}$$

For 1W of output power into an 8 $\Omega$  load, the required V<sub>opeak</sub> is 4.0V. A minumum supply rail of 4.6V results from adding V<sub>opeak</sub> and V<sub>od</sub>. But 4.6V is not a standard voltage that exists in many applications and for this reason, a supply rail of 5V is designated. Extra supply voltage creates dynamic headroom that allows the LM4861 to reproduce peaks in excess of 1Wwithout clipping the signal. At this time, the designer must make sure that the power supply choice along with the output impedance does not violate the conditions explained in the **Power Dissipation** section.

Once the power dissipation equations have been addressed, the required differential gain can be determined from Equation 4.

$$A_{VD} \ge \sqrt{(P_0 R_L)} / (V_{IN}) = V_{orms} / V_{inrms}$$

$$(4)$$

$$R_{I} / R_i = A_{VD} / 2$$

$$(5)$$

From equation 4, the minimum  $A_{vd}$  is 2.83:  $A_{vd}$  = 3


Since the desired input impedance was  $20k\Omega$ , and with a  $A_{vd}$  of 3, a ratio of 1:1.5 of  $R_f$  to  $R_i$  results in an allocation of  $R_i = 20k\Omega$ ,  $R_f = 30k\Omega$ . The final design step is to address the bandwidth requirements which must be stated as a pair of -3dB frequency points. Five times away from a -3db point is 0.17dB down from passband response which is better than the required ±0.25dB specified. This fact results in a low and high frequency pole of 20Hz and 100kHz respectively. As stated in the **External Components** section,  $R_i$  in conjunction with  $C_i$  create a highpass filter.

 $C_i \ge 1 / (2\pi^* 20 k\Omega^* 20 Hz) = 0.397 \mu F$ ; use  $0.39 \mu F$ .

The high frequency pole is determined by the product of the desired high frequency pole,  $f_{\rm H}$ , and the differential gain,  $A_{\rm vd}$ . With a  $A_{\rm vd}$  = 2 and  $f_{\rm H}$  = 100kHz, the resulting GBWP = 100kHz which is much smaller than the LM4861 GBWP of 4MHz. This figure displays that if a designer has a need to design an amplifier with a higher differential gain, the LM4861 can still be used without running into bandwidth problems.

## LM4861 MDA MWA

1.1W Audio Power Amplifier with Shutdown Mode




## **DIE/WAFER CHARACTERISTICS**

Fabrication Attributes			General Die Information				
Physical Die Identification		LM4	861B	Bond Pad Opening Size (min)		83µm x 83µm	
Die Step		В	B Bond Pad Metalization		zation	ALUMINUM	
	Physical Attr	ibutes		Passivation		VOM NITRIDE	
Wafer Diameter		150	mm	Back Side Metal Back Side Connection		BARE BACK	
Dise Size (Draw	n)	137	2µm x 2032µm			GND	
		54.0	mils x 80.0mils				
Thickness		406	µm Nominal		<b>I</b>		
Min Pitch		108	µm Nominal				
Special Assem	bly Requirements:			·			
•	ie size is rounded to	o the nearest	micron.				
		Die Bond Pa	d Coordinate Loo	ations (B - Step)			
	(Referenced to die			c = No Connection,	N.U. = Not Used		
		1	OORDINATES	PAD SIZE			
SIGNAL NAME	PAD# NUMBER	X	Y	Х		Y	
SHUTDOWN	1	-425	710	83	x	83	
BYPASS	2	-445	499	83	x	83	
NC	3	-445	-34	83	x	170	
NC	4	-445	-383	83	x	83	
INPUT +	5	-445	-492	83	x	83	
INPUT -	6	-352	-710	83	x	83	
GND	7	-243	-710	83	x	83	
Vo1	8	-91	-710	170	x	83	
GND	9	445	-574	83	x	170	
VDD	10	445	-2	83	x	170	
NC	11	445	387	83	x	83	
GND	12	445	633	83	x	170	
Vo2	13	-63	710	170	x	83	
GND	14	-215	710	83	x	83	

LM4861

## LM4861 MDA MWA 1.1W Audio Power Amplifier with Shutdown Mode (Continued)

IN U.S.A		
Tel #:	1 877 Dial Die 1 877 342 5343	
Fax:	1 207 541 6140	
IN EUROPE		
Tel:	49 (0) 8141 351492 / 1495	
Fax:	49 (0) 8141 351470	
IN ASIA PACIFIC		
Tel:	(852) 27371701	
IN JAPAN		
Tel:	81 043 299 2308	



NATIONAL'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS WITHOUT THE EXPRESS WRITTEN APPROVAL OF THE PRESIDENT AND GENERAL COUNSEL OF NATIONAL SEMICONDUCTOR CORPORATION. As used herein:

CONTROLLING DIMENSION IS INCH VALUES IN [] ARE MILLIMETERS

Order Number LM4861 NS Package Number M08A

- 1. Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body, or (b) support or sustain life, and whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in a significant injury to the user.
- 2. A critical component is any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

National Semiconductor Americas Customer Support Center Email: new.feedback@nsc.com Tel: 1-800-272-9959

www.national.com

National Semiconductor Europe Customer Support Center Fax: +49 (0) 180-530 85 86 Email: europe.support@nsc.com Deutsch Tel: +49 (0) 69 9508 6208 English Tel: +44 (0) 870 24 0 2171 Français Tel: +33 (0) 1 41 91 8790

National Semiconductor Asia Pacific Customer Support Center Fax: 65-6250 4466 Email: ap.support@nsc.com Tel: 65-6254 4466

45°X.017-

(.041 [1.04]

DETAIL A TYPICAL, SCALE: 40X

-SEE DETAIL A

SEATING PLANE

.0075-.0098 [0.19-0.25] TYP

M08A (Rev J)

R.007±.001 [0.18±0.02]

R.009±.001 [0.23±0.02] 0° - 8


.016-.050

.154±.004 [3.<u>91±0</u>.1]

- B -

(.057 [1.45]

National Semiconductor Japan Customer Support Center Fax: 81-3-5639-7507 Email: nsj.crc@jksmtp.nsc.com Tel: 81-3-5639-7560



National does not assume any responsibility for use of any circuitry described, no circuit patent licenses are implied and National reserves the right at any time without notice to change said circuitry and specifications.

#### **IMPORTANT NOTICE**

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, modifications, enhancements, improvements, and other changes to its products and services at any time and to discontinue any product or service without notice. Customers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its hardware products to the specifications applicable at the time of sale in accordance with TI's standard warranty. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by government requirements, testing of all parameters of each product is not necessarily performed.

TI assumes no liability for applications assistance or customer product design. Customers are responsible for their products and applications using TI components. To minimize the risks associated with customer products and applications, customers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any TI patent right, copyright, mask work right, or other TI intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information published by TI regarding third-party products or services does not constitute a license from TI to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. Reproduction of this information with alteration is an unfair and deceptive business practice. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI products or services with statements different from or beyond the parameters stated by TI for that product or service voids all express and any implied warranties for the associated TI product or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

TI products are not authorized for use in safety-critical applications (such as life support) where a failure of the TI product would reasonably be expected to cause severe personal injury or death, unless officers of the parties have executed an agreement specifically governing such use. Buyers represent that they have all necessary expertise in the safety and regulatory ramifications of their applications, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of TI products in such safety-critical applications, notwithstanding any applications-related information or support that may be provided by TI. Further, Buyers must fully indemnify TI and its representatives against any damages arising out of the use of TI products in such safety-critical applications.

TI products are neither designed nor intended for use in military/aerospace applications or environments unless the TI products are specifically designated by TI as military-grade or "enhanced plastic." Only products designated by TI as military-grade meet military specifications. Buyers acknowledge and agree that any such use of TI products which TI has not designated as military-grade is solely at the Buyer's risk, and that they are solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI products are neither designed nor intended for use in automotive applications or environments unless the specific TI products are designated by TI as compliant with ISO/TS 16949 requirements. Buyers acknowledge and agree that, if they use any non-designated products in automotive applications, TI will not be responsible for any failure to meet such requirements.

Following are URLs where you can obtain information on other Texas Instruments products and application solutions:

Products		Applications	
Audio	www.ti.com/audio	Communications and Telecom	www.ti.com/communications
Amplifiers	amplifier.ti.com	Computers and Peripherals	www.ti.com/computers
Data Converters	dataconverter.ti.com	Consumer Electronics	www.ti.com/consumer-apps
DLP® Products	www.dlp.com	Energy and Lighting	www.ti.com/energy
DSP	dsp.ti.com	Industrial	www.ti.com/industrial
Clocks and Timers	www.ti.com/clocks	Medical	www.ti.com/medical
Interface	interface.ti.com	Security	www.ti.com/security
Logic	logic.ti.com	Space, Avionics and Defense	www.ti.com/space-avionics-defense
Power Mgmt	power.ti.com	Transportation and Automotive	www.ti.com/automotive
Microcontrollers	microcontroller.ti.com	Video and Imaging	www.ti.com/video
RFID	www.ti-rfid.com		
OMAP Mobile Processors	www.ti.com/omap		
Wireless Connectivity	www.ti.com/wirelessconnectivity		
		u Hama Dawa	a O a Al a a m

**TI E2E Community Home Page** 

e2e.ti.com

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2011, Texas Instruments Incorporated