

CABLE DRAWING

Habia Cable

Type: RG 196A/U	Habia inspection plan		Date of issue 1991-04-04		Drawing no 30000-196-00
	Issued by POM	Approved by EJ	Rev. no	Revised by	Revised date

Elektriska data vid + 20 °C / Electrical data at +20 °C (nom. data)


1 (1)

LEDARRESISTANS / CONDUCTOR RESISTANCE	max 802	OHMS/km
ISOLATIONSRESISTANS / INSULATION RESISTANCE	>5000	MOHMS x km
KAPACITANS / CAPACITANCE	nom 94 max 105	nF/ km
IMPEDANS / IMPEDANCE	50±2	OHMS
DÄMPNING / ATTENUATION	400 MHz max 108	dB/100 m
PROVSPÄNNING / TEST VOLTAGE	1 min 2	kV AC
DRIFTSTEMPERATUR / TEMPERATURE RATING	-55/+200	°C
DRIFTSPÄNNING / VOLTAGE RATING		VOLTS
VIKT / WEIGHT		kg/km

This drawing remains a property of HABIA CABLE and it is forbidden to copy, show or give it to third part or other unauthorized persons without our written permission.

Pos	Beskrivning/Description	Dimensioner/Dimensions	Yterdiam./ Overall diam.	Anm./Remarks
1	Silverplated copper covered steelwire	SCWS	0,30	7x0,102
2	Dielectric of PTFE		0,84	
3	Braid of silverplated copper wire	wire diam 0,10	1,3	
4	Jacket of PTFE, white		1,94	

Sparktest jacket 2 kV AC



Habia Cable förbehåller sig rätten att ändra ingående material till annat likvärdigt material utan att meddela kund. Habia Cable reserves the right to change any material, dimensions or parameters without notice.