



Key, MS2-20, according to data

Part no. **M22-ES-MS\***  
Article no. **216417**  
Catalog No. **-**

## Delivery programme

Product range			RMQ-Titan (drilling dimensions 22.5 mm)
Basic function			Accessories
Basic function accessories			Individual keys
Description			Lock mechanism MS2 – MS20
For use with			M22(S)-W(R)S(3)-MS*...
Connection to SmartWire-DT			no

## Technical data

### General

Ambient temperature			
Open		°C	-25 - +70

## Design verification as per IEC/EN 61439

Technical data for design verification			
Operating ambient temperature min.		°C	-25
Operating ambient temperature max.		°C	70

## Technical data ETIM 6.0

Low-voltage industrial components (EG000017) / Accessories for control circuit devices (EC002024)			
Electric engineering, automation, process control engineering / Low-voltage switch technology / Low-voltage switch technology (accessories) / Control circuit devices (accessories) (ecl@ss8.1-27-37-92-16 [AC0043008])			
Type of electrical accessory			-
Type of mechanical accessory			Key

## Approvals

North America Certification			UL/CSA certification not required
-----------------------------	--	--	-----------------------------------