


SPECIFICATION FOR APPROVAL

CERAMIC DISC CAPACITORS		Issue No.				
CUSTOMER :		Issue Day. 12/12/2012				
Capacitance: 120 pF	Tolerance: ±5 %	W V 100 VDC				
Temp. Coef. NPO	Q'ty of Sample: _____ pcs	Your Confirmation				
Cust. P/N:	Part No. TCH2A121J-S265B	APPROVAL				
Shape & Dimension	Unit : mm					
 <p>D: <u>7.0 max.</u> T: <u>2.5 max.</u> F: <u>2.54 ± 0.8</u> L: <u>6.0 ± 0.8</u> d: <u>0.5 ± 0.05</u> P: <u>2.0 max.</u></p>		CONDITIONAL APPROVAL				
		REJECTION				
		(Please send a copy for our ref.)				
SPECIFICATION		Initial Test				
		No.	pF	Tanδ	I.R.	T.V.
Frequency = 1M Hz Temperature = 25 °C		1.				
1	Initial Q : 1,000 Min.	2.				
2	Initial IR : 10,000 MΩ Min.	3.				
3	Dielectric Strength Test : DC 250 V	4.				
4	Case Insulation Test : DC 100 V	5.				
5	Temperature Characteristics : 0 ± 60 PPM/°C	6.				
6	Lead Pull Test : 1.0 Kg 5 Seconds.	7.				
		8.				
		9.				
		10.				
Remark :						
Spec. Applied by EIA RS198						
Test Instruments:						
(1). Capacitance:						
(a).CHEN HWA 1062 L.C.R.METER (1Khz). (b).ESI410 OR HP 4277 L.C.R.METER (1Mhz).						
(2). Dissipation Factor: as the Item (1).						
(3). Insulation Resistance: GENERAL RADIO 1864 MEGOHM METER.						
(4).Dielectric Strength: PHIHON PUNCTURE TESTER.						
Inspected by		Checked by	吳美華	Approved by	許介洲	