

GN 192.1 | T-shaped connecting clamps

for linear actuators, aluminium



- 1
- 2
- 3
- 4
- 5
- 6
- 7
- 8
- 9
- 10
- 11
- 12
- 13
- 14
- 15
- 16
- 17
- 18
-

MATERIAL

Aluminium, epoxy resin coating, RAL 9005 black colour, matte finish.
AISI 304 stainless steel screws and nuts.



STANDARD EXECUTIONS

- **GN 192.1-B-B**: without sliding bushing.
- **GN 192.1-G-B**: with a polyamide based (PA) or polytetrafluoroethylene based (PTFE) technopolymer sliding bushing (d1).

FEATURES AND APPLICATIONS

GN 192.1 clamping connectors can normally be matched with the linear actuators.

By clamping the guide hole d1 it is possible to adjust the actuator positioning and to lock the slider after having set up the final position. The clamping screws d3 may be replaced by clamping kits GN 911 (see page 1782).



Code	Description	d1#	d1##	d2	d3	d4	k1	k2	l	m	d3 Clamping kit	⚖️
GN.52706	GN 192.1-B30-B30-2-SW	30	-	30	M8	M4	40	42.5	92	60	GN 911-M8-32	185
GN.52716	GN 192.1-B40-B40-2-SW	40	-	40	M10	M5	56	62	129	88	GN 911-M10-40	450
GN.52726	GN 192.1-B50-B50-2-SW	50	-	50	M10	M6	65	75	148	103	GN 911-M10-55	620
GN.52736	GN 192.1-B60-B60-2-SW	60	-	60	M10	M8	80	80	177	125	GN 911-M10-55	1260
GN.52746	GN 192.1-G30-B30-2-SW	-	30	30	M8	M4	40	42.5	92	60	GN 911-M8-32	185
GN.52756	GN 192.1-G40-B40-2-SW	-	40	40	M10	M5	56	62	129	88	GN 911-M10-40	450
GN.52766	GN 192.1-G50-B50-2-SW	-	50	50	M10	M6	65	75	148	103	GN 911-M10-55	620
GN.52776	GN 192.1-G60-B60-2-SW	-	60	60	M10	M8	80	80	177	125	GN 911-M10-55	1260

Hole without sliding bushing.

Hole with sliding bushing.

Connecting clamps

1806



11/2019

Models all rights reserved in accordance with the law. Always mention the source when reproducing our drawings and photos.

