# productinformation

## tesa® 4965

### 205µm double sided transparent filmic tape

tesa® 4965 is a transparent, double-sided self-adhesive tape consisting of a PET backing and a tackyfied acrylic adhesive.

tesa® 4965 features especially:

- Reliable bond even on hard to stick surfaces
- Immediate usability right after assembly
- Suitability for critical demands such as heavy stress and high temperatures

## Main Application

Based on tesa® 4965's patented and protected techology, its unique performance is demonstrated through outstanding qualities such as versatility, durability and safety. Across all industries tesa® 4965 is used to improve processes and applications. Key applications include:

- ABS plastics parts mounting for the car industry
- Self-adhesive mounting for rubber/EPDM profiles
- Decorative moulding and profile mounting in the furniture industry
- Battery pack, lens and touch-screen mounting for electronic devices

4965 is recognized according to UL standard 969. UL file: MH 18055

Certificate available according to DIN EN 45545-2 fulfilling 2R1+HL3

#### Technical Data

•	Backing material	PET film	•	Type of adhesive	tackified acrylic
•	Color	transparent	•	Elongation at break	50 %
•	Total thickness	205 μm	•	Tensile strength	20 N/cm

#### Adhesion to

<ul> <li>Steel (initial)</li> <li>11.5 N/cm</li> <li>Steel (after 14 days)</li> </ul>	11.8 N/cm
<ul> <li>ABS (initial)</li> <li>10.3 N/cm</li> <li>ABS (after 14 days)</li> </ul>	12.0 N/cm
<ul> <li>Aluminium (initial)</li> <li>9.2 N/cm</li> <li>Aluminium (after 14 days)</li> </ul>	10.6 N/cm
<ul> <li>PC (initial)</li> <li>12.6 N/cm</li> <li>PC (after 14 days)</li> </ul>	14.0 N/cm
<ul><li>PE (initial)</li><li>5.8 N/cm</li><li>PE (after 14 days)</li></ul>	6.9 N/cm
<ul> <li>PET (initial)</li> <li>9.2 N/cm</li> <li>PET (after 14 days)</li> </ul>	9.5 N/cm
<ul><li>PP (initial)</li><li>6.8 N/cm</li><li>PP (after 14 days)</li></ul>	7.9 N/cm
<ul><li>PS (initial)</li><li>10.6 N/cm</li><li>PS (after 14 days)</li></ul>	12.0 N/cm
<ul> <li>PVC (initial)</li> <li>8.7 N/cm</li> <li>PVC (after 14 days)</li> </ul>	13.0 N/cm

For latest information on this product please visit <a href="http://l.tesa.com/?ip=04965">http://l.tesa.com/?ip=04965</a>



## tesa® 4965

## 205µm double sided transparent filmic tape

#### **Properties**

- Temperature resistance short termTemperature resistance long term
- Tack
- Ageing resistance (UV)
- Humidity resistance

- 200 °C 100 °C
- •••
- Resistance to chemicals
- Softener resistance
- Static shear resistance at 23°C
- Static shear resistance at 40°C



Evaluation across relevant tesa® assortment: ••• very good •• good •• medium • lov

#### Additional Information

Liner variants:

PV0: red MOPP-film (80μm; 72g/m²) PV1: brown glassine paper (69μm; 80g/m²) PV2: brown glassine paper (78μm; 90g/m²)

PV4: branded white paper liner ( $104\mu m$ ;  $120g/m^2$ ) PV8: white MOPP friction liner ( $80\mu m$ ;  $72g/m^2$ ) PV20: branded brown paper liner ( $69\mu m$ ;  $80g/m^2$ )

This product information applies to PV1

According to VDA278 analysis, tesa 4965 does not contain any single substances restricted by the drafted GB regulations (China) as well as the indoor concentration guideline by Health, Labour and Welfare Ministry (Japan).