


# Safety isolating transformer AVB 1,5/2/6



Picture shows AVB 3,2/2/18

## Advantages


- Minimum size at high output
- Inherently short-circuit proof
- Dual input voltage for series or parallel connection
- Also with dual output voltage for series or parallel connection
- Designed for high ambient temperatures
- Permanent corrosion protection, high insulation value and maximum electrical reliability thanks to XtraDenseFill resin encapsulation
- Self-extinguishing potting and hood material

## Applications

As a mains transformer for adjustment of the voltage and simple electrical isolation.

As a safety transformer for the safe electrical isolation of the input and output sides. The transformer is suitable for creating SELV and PELV circuits because of the limit on the output voltage.

## Sample application




## Standards

Safety isolating transformer  
to: VDE 0570 Part 2-6, DIN EN 61558-2-6, EN 61558-2-6, IEC 61558-2-6,  
UL 5085-1/-2, CSA 22.2 No.66

## Approvals



UL 5085-1/-2, CSA 22.2 No.66




# Safety isolating transformer

## AVB 1,5/2/6

Electrical data	
Type	AVB 1,5/2/6
<b>Input</b>	
Rated input voltage	2 x 115 Vac
Rated frequency	50 - 60 Hz
<b>Output</b>	
Rated output voltage	2 x 6 Vac
Rated Power	1.5 VA
No-load voltage (app. x factor)	1.39
No-load loss (typ.)	1.00 W
Efficiency	57.0 %
<b>Standards</b>	
Classification	Safety isolating transformer
<b>Approvals</b>	
Approvals	cURus
<b>Environment</b>	
Ambient temperature max.	70 °C
<b>Safety and protection</b>	
Type	Encapsulated
Insulation class	VDE=B, UL=class 105
Protection index	IP 00
Safety class (prepared)	II
Short circuit strength	inherently short-circuit proof
<b>Order numbers</b>	
<b>Order Number</b>	<b>AVB 1,5/2/6</b>

Mechanical data	
Type	AVB 1,5/2/6
<b>Terminal and mounting</b>	
Terminals	Pins for printed circuit boards
Pin (ø)	0.8
<b>Measures and weights</b>	
Core type	EI 30/12,5
Weight	0.08 kg



Subject to change.