







# 1300 SERIES CRIMP TOOL

The 1300 Series Crimp tool is comprised of a universal tool frame and a comprehensive range of interchangeable dies. Designed for most popular interconnect applications this fully ratcheting tool utilises hardened dies for long life. A high impact storage case is available for the frame and selected dies.

| Part No. | Crimp Size (mm)  |  |  |  |  |  | Application                                  |
|----------|--|--|--|--|--|--|--|
|          |  |  |  |  |  |  |  |
|          |  |  |  |  |  |  | <b>COAX</b>                                  |
| 2027     |  |  |  |  | 5.33   | 1.24   | RG58, BNC, TNC, AMP                          |
| 2028     |  |  |  |  | 6.30   | 1.24   | RG59, 62AU, BNC, TNC, AMP                    |
| 2034     | 6.50   | 5.41   | 1.73   |  |  |  | RG58, 59, 62AU, BNC, TNC                     |
| 2039     | 10.54  |  | 2.41   |  |  |  | N Type for RG8, 11, 213, 216 cable.          |
| 2041     | 8.00   | 5.79   | 1.73   |  |  |  | Cambridge CP88 and CP89                      |
| 2042     | 8.78   | 8.00   | 6.50   | 1.07   |  |  | F Type for RG6, 59 cable.                    |
| 2046     | 5.41   | 4.52   | 1.73   | 1.07   |  |  | RG58, 174, 50 and 75 ohm.                    |
| 2047     | 8.00   | 6.40   | 1.73   | 2.00   |  |  | RG59, 828, 50 and 75 ohm.                    |
| 2050     | 10.21  |  | 2.39   |  |  |  | RG8, BNC                                     |
| 2051     | 4.52   | 3.25   | 1.73   |  |  |  | RG174  |
| 2075     | 8.25   | 5.46   | 1.65   |  |  |  | RG58, 59, 62 teflon BNC, TNC.                |
| 2076     | 8.13   | 5.33   | 4.70   |  |  |  | RG6, 58, BNC (Amphenol & Kings)              |
| 2084     | 10.90  |  | 2.54   |  |  |  | N Type RG213 Amphenol                        |
|          |  |  |  |  |  |  | <b>TERMINALS &amp; SPLICES</b>               |
| 2029     |  |  |  |  |  |  | 14-26 AWG Terminal & Splices insulated       |
| 2031     |  |  |  |  |  |  | 14-22 AWG Terminal & Splices non-insulated   |
| 2033     |  |  |  |  |  |  | 14-22 AWG Open barrel non-insulated contacts |
| 2035     |  |  |  |  |  |  | 14-22 AWG Terminal & Splices insulated       |
| 2040     |  |  |  |  |  |  | 14-22 AWG Terminal & Splices insulated max   |
|          |  |  |  |  |  |  | <b>FIBRE OPTIC</b>                           |
| 2043     | 5.46   | 4.52   | 3.83   |  |  |  | Universal fibre optic.                       |
|          |  |  |  |  |  |  | <b>TELEPHONE PLUGS</b>                       |
| 2061     |  |  |  |  |  |  | RJ45 Stewart/WE type                         |
| 2062     |  |  |  |  |  |  | RJ11 Stewart/WE type                         |
| 2063     |  |  |  |  |  |  | Handset We type                              |
| 2064     |  |  |  |  |  |  | RJ45 AMP                                     |
| 2065     |  |  |  |  |  |  | RJ11 AMP                                     |
| 2067     |  |  |  |  |  |  | RJ11 DEC-MMJ AMP                             |
| 2068     |  |  |  |  |  |  | RJ45 10 position AT&T application            |

| Part No.  | Description       |
|-----------|-------------------|
| 1302      | 1300 Tool Frame   |
| 9582.1920 | 1300 Storage Case |