

## Metal circular saw blade, HSS, coarse-toothed with taper tap and third tap, type C

for universal use up to 1000 N/mm<sup>2</sup> in larger cross sections and cutting depths on conventional machines

**ORION**<sup>®</sup>

### Application:


For creating separation cuts in medium to large cutting depths in the material groups of steel, (stainless steel), cast iron and (non-ferrous metals) up to a strength of 1000 N/mm<sup>2</sup>.

### Execution:

- precision-ground metal circular saw blade with tooth type B, coarse serrated with taper tap and third tap, laterally hollow-ground, hole without keyway

### Advantage:

- innovative cutting geometry with large chip space plus taper tap and third tap ensures cutting distribution and increases cutting performance
- top-quality cutting material for extremely demanding requirements in terms of service life
- universal use for a multitude of applications



<b>Art. no.</b>	<b>14008 400</b>
<b>Brand</b>	ORION
<b>Manufacturer Part Number</b>	14008400
<b>Tooth shape</b>	C
<b>Cutting material</b>	HSS
<b>Thickness of cutting edge</b>	1.6 mm
<b>Tolerance of cutting edge diameter</b>	js15
<b>Tolerance of cutting edge thickness</b>	js11
<b>Tolerance of hole diameter</b>	H7
<b>Cutting edge diameter</b>	80 mm
<b>Bore diameter</b>	22 mm
<b>Number of teeth</b>	48 PCS
<b>DIN</b>	1838
<b>Form</b>	C, extra narrow
<b>Gross Weight</b>	0.057 kg
<b>Product Group</b>	1QK

### EAN

403924707997 1