

## Measuring instrument - EEM-MA770 - 2907945


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Multi-functional energy measuring device with integrated Modbus/TCP interface for measuring electrical parameters in low-voltage installations up to 690 V.



### Key Commercial Data

Packing unit	1 pc
GTIN	 4 055626 260389
GTIN	4055626260389
Weight per Piece (excluding packing)	531.000 g
Sales Key	CK4C21

### Technical data

#### Dimensions

Width	96 mm
Height	96 mm
Depth	58 mm

#### Ambient conditions

Ambient temperature (operation)	-10 °C ... 55 °C
Ambient temperature (storage/transport)	-40 °C ... 70 °C
Maximum altitude	≤ 2000 m
Max. permissible relative humidity (operation)	≤ 95 % (non-condensing)
Degree of protection	IP52 (Display (+ EEM-MA-IP))
	IP20 (Housing)

#### Input data

Measuring principle	True r.m.s. value measurement (TRMS)
Acquisition of harmonics	up to 63rd harmonic
Measured value	AC sine (50/60 Hz)
Input name	Voltage measuring input V1, V2, V3

# Measuring instrument - EEM-MA770 - 2907945

## Technical data

### Input data

Input voltage range	35 V AC ... 690 V AC (Phase/Phase)
	20 V AC ... 400 V AC (Phase/neutral conductor)
	60 V AC ... 2000000 V AC (primary)
	60 V AC ... 400 V AC (secondary)
Surge voltage capacity	760 V AC (Phase/Phase)
Precision	0.2 %
Input name	Current measurement I1, I2, I3
Input current	1 A (secondary)
	5 A (secondary)
Current measuring range	1 A ... 20000 A (primary)
Overload capacity	6 A (I <sub>max</sub> )
Response threshold from measuring range nominal value	10 mA (1 A)
Precision	0.2 %
Current overload	50 A for 1 s
Precision	0.5 %
Active energy (IEC 62053-22)	Class 0.5 S
Reactive power (IEC 62053-23)	Class 2
Description of the input	Digital input in accordance with IEC/EN 61131-2 (type 3)
Number	1
Voltage input signal	0 V DC ... 30 V DC
Current input signal	2 mA ... 15 mA

### Output data

Output description	Digital output in accordance with IEC/EN 61131-2 (type 3)
Number	1
Current output signal	≤ 100 mA

### General

Display	LCD display, two-color backlit
Supply voltage range	100 V AC ... 400 V AC (# 20 %)
Power consumption	≤ 4 W
Mains type	3-phase (3 or 4-wire), 2-phase (2-wire), and single-phase (1-wire)
Color	gray
Conformance	CE-compliant
Test voltage	4 kV AC (50 Hz, 1 min.)
Product family	EMpro

### Connection data

Connection name	Current / voltage / supply
Connection method	Screw connection
Stripping length	8 mm
Screw thread	M3

# Measuring instrument - EEM-MA770 - 2907945

## Technical data

### Connection data

Conductor cross section solid	0.2 mm <sup>2</sup> ... 6 mm <sup>2</sup>
Conductor cross section flexible	0.2 mm <sup>2</sup> ... 4 mm <sup>2</sup>
Conductor cross section AWG	24 ... 10
Torque	0.5 Nm ... 0.6 Nm

### Connection data 2

Connection name	Digital I/O / communication
Connection method	Screw connection
Stripping length	7 mm
Screw thread	M3
Conductor cross section solid	0.14 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Conductor cross section flexible	0.14 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>
Conductor cross section AWG	26 ... 14
Torque	0.5 Nm ... 0.6 Nm

### UL data

Operating mode	Indoor use
----------------	------------

### Standards and Regulations

Conformance	CE-compliant
-------------	--------------

### Environmental Product Compliance

China RoHS	Environmentally Friendly Use Period = 50
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

## Classifications

### eCl@ss

eCl@ss 5.0	27200301
eCl@ss 5.1	27200301
eCl@ss 6.0	27142300
eCl@ss 7.0	27142330
eCl@ss 8.0	27142330
eCl@ss 9.0	27142330

### ETIM

ETIM 4.0	EC002301
ETIM 5.0	EC002301
ETIM 6.0	EC002301
ETIM 7.0	EC002301

## Measuring instrument - EEM-MA770 - 2907945

### Approvals

Approvals

---

Approvals

EAC

---

Ex Approvals

---

### Approval details

EAC		RU*DE*08.B.00734/19
-----	---	---------------------

### Accessories

Accessories

Assembly adapter

DIN rail adapter - EEM-MKT-DRA - 2902078



DIN rail adapter for EEM-MA600 and EEM-MA400 energy meters

---

---