



Type Designation	2014
Designation IEC	R14 P
System	Carbon Zinc
Shelf Life (Coding)*	36 months
Nominal Voltage [V]	1.5
Typical Capacity C [mAh]	3000 (discharge with high-resistance)
Permissible Temperature Range	- 10 °C ... 50 °C
Weight, approx. [g]	47.1
Volume [ccm]	26.5

Dimensions [mm]

	min:	max:
∅	24.9	26.2
A	-	50.0
B	48.6	-
C	13.0	-
E	-	0.9
F	-	7.5
G	1.5	-



Typical Capacities (at 20°C)

Discharge Type	Load	End Voltage[V]	0.9
4M/H, 8H/D, 7D/W	3.9 Ω	Time [m]	350
Portable lighting		Capacity [Ah]	1.7
		Energy [Wh]	2.0
Discharge Type	Load	End Voltage[V]	0.8
1H/D, 7D/W	3.9 Ω	Time [h]	6.75
Toy		Capacity [Ah]	1.8
		Energy [Wh]	2.0

No publication or circulation of data to third parties without consent of VARTA Consumer Batteries

* In consideration of typical loss of capacity at storage and application.