Surface Mount Fuse, 1.6 x 0.8 mm, Super-Quick-Acting FF, 32 VAC, 63 VDC



UL 248-14 · 63 VAC · 63 VDC · Super-Quick-Acting FF

See below:

Approvals and Compliances

Description

- UL characteristic
- Low melting I2t-values, fast interruption
- Impermeable to potting compound

Applications

- Secondary Protection DC and AC
- Circuits without inrush
- Semiconductor protection

Weblinks

pdf data sheet, html datasheet, General Product Information, Distributor-Stock-Check, Detailed request for product, Microsite

Technical Data	
Rated Voltage	63 VAC, 63 VDC
Rated current	0.5 - 5A
Breaking Capacity	50A
Characteristic	Super-Quick-Acting FF
Mounting	PCB,SMT
Admissible Ambient Air Temp.	-55 °C to 90 °C
Climatic Category	55/090/21 acc. to IEC 60068-1
Material: Housing	Fiber-reinforced plastic, UL 94V-0
Material: Terminals	Copper, Ni/Au-plated
Unit Weight	0.0016 g
Storage Conditions	0°C to 60°C, max. 70% r.h.
Product Marking	Letter (see variants)

Reflow
Soldering Profile
245°C / 3 sec acc. to IEC 60068-2-58,
Test Td
260 +0/-5 °C / 30 sec acc. to IPC/JE-
DEC J-STD-020D, Level 1
MSL 1, J-STD-020
acc. to EIA/IS-722, Test 4.7
>100 MΩ (between leeds and body)
min. UL 94V-1
(acc. to EIA/IS-722, Test 4.12)
MIL-STD-202, Method 106
(50 cycles in a temp./mister chamber)
MIL-STD-202, Method 215
MIL-STD-202, Method 211A
(Deflection of board 1 mm for 1 minute)

Approvals and Compliances

Detailed information on product approvals, code requirements, usage instructions and detailed test conditions can be looked up in Details about Approvals

SCHURTER products are designed for use in industrial environments. They have approvals from independent testing bodies according to national and international standards. Products with specific characteristics and requirements such as required in the automotive sector according to IATF 16949, medical technology according to ISO 13485 or in the aerospace industry can be offered exclusively with customer-specific, individual agreements by SCHURTER.

Approvals

The approval mark is used by the testing authorities to certify compliance with the safety requirements placed on electronic products. Approval Reference Type: USF 0603

Approval Logo Certificates Description Certification Body **UL Approvals** UL UR File Number: E41599 .**91**°118

Product standards

Product standards that are referenced

Organization Design Standard Description

UL 248-14 Low voltage fuses - Part 14: Additional fuses

Designed according to CSA22.2 No. 248.14 Low-Voltage Fuses - Part 14: Supplemental Fuses

Application standards

Application standards where the product can be used

OrganizationDesignStandardDescriptionIECBesigned for applications acc.IEC/UL 62368-1Audio/video, information and communication technology equipment - Part 1: Safety requirements


Compliances

The product complies with following Guide Lines

Identification	Details	Initiator	Description
C€	CE declaration of conformity	SCHURTER AG	The CE marking declares that the product complies with the applicable requirements laid down in the harmonisation of Community legislation on its affixing in accordance with EU Regulation 765/2008.
UK CA	UKCA declaration of conformity	SCHURTER AG	The UKCA marking declares that the product complies with the applicable requirements laid down in the British Amendment of Regulation (EC) 765/2008.
RoHS	RoHS	SCHURTER AG	Directive RoHS 2011/65/EU, Amendment (EU) 2015/863
©	China RoHS	SCHURTER AG	The law SJ / T 11363-2006 (China RoHS) has been in force since 1 March 2007. It is similar to the EU directive RoHS.
Halogen Free 🕼	Halogen Free	SCHURTER AG	SCHURTER strives to offer our customers halogen free products.
REACH	REACH	SCHURTER AG	On 1 June 2007, Regulation (EC) No 1907/2006 on the Registration, Evaluation, Authorization and Restriction of Chemicals 1 (abbreviated as "REACH") entered into force.

Dimension [mm]

H 1.6 mm






Soldering pads

Pre-Arcing Time

Rated Current In 1.0 x In min. 2.0 x In max.

0.5 A - 5 A 4 h 60 s

Time-Current-Curves



Current in Amperes

All Variants

Rated Cur- rent [A]	Rated Voltage [VAC]	Rated Vol- tage [VDC]	Marking	Breaking Capacity	Voltage Drop 1.0 I _n typ. [mV]	Cold Resistance typ. [mΩ]	Melting I ² t 8.0 I _n typ. [A ² s]	c 711 'us	Order Number
0.5	32	63	F	1)	125	225	0.025	•	3412.0113.11
0.5	32	63	F	1)	125	225	0.025	•	3412.0113.22
0.5	32	63	F	1)	125	225	0.025	•	3412.0113.24
0.5	32	63	F	1)	125	225	0.025	•	3412.0113.26
0.75	32	63	G	1)	110	120	0.05	•	3412.0114.11
0.75	32	63	G	1)	110	120	0.05	•	3412.0114.22
0.75	32	63	G	1)	110	120	0.05	•	3412.0114.24
0.75	32	63	G	1)	110	120	0.05	•	3412.0114.26
1	32	63	Н	1)	110	95	0.06	•	3412.0115.11
1	32	63	Н	1)	110	95	0.06	•	3412.0115.22
1	32	63	Н	1)	110	95	0.06	•	3412.0115.24
1	32	63	Н	1)	110	95	0.06	•	3412.0115.26
1.5	32	63	K	1)	65	37.5	0.15	•	3412.0117.11
1.5	32	63	K	1)	65	37.5	0.15	•	3412.0117.22
1.5	32	63	K	1)	65	37.5	0.15	•	3412.0117.24
1.5	32	63	K	1)	65	37.5	0.15	•	3412.0117.26
2	32	32	N	2)	65	28	0.2	•	3412.0119.11
2	32	32	N	2)	65	28	0.2	•	3412.0119.22
2	32	32	N	2)	65	28	0.2	•	3412.0119.24
2	32	32	N	2)	65	28	0.2	•	3412.0119.26
2.5	32	32	0	2)	60	21.5	0.29	•	3412.0120.11
2.5	32	32	0	2)	60	21.5	0.29	•	3412.0120.22
2.5	32	32	0	2)	60	21.5	0.29	•	3412.0120.24
2.5	32	32	0	2)	60	21.5	0.29	•	3412.0120.26
3	32	32	Р	2)	60	17	0.32	•	3412.0121.11
3	32	32	Р	2)	60	17	0.32	•	3412.0121.22
3	32	32	Р	2)	60	17	0.32	•	3412.0121.24
3	32	32	Р	2)	60	17	0.32	•	3412.0121.26

Rated Cur- rent [A]	Rated Voltage [VAC]	Rated Vol- tage [VDC]	Marking	Breaking Capacity	Voltage Drop 1.0 I _n typ. [mV]	Cold Resistance typ. [mΩ]	Melting I ² t 8.0 I _n typ. [A ² s] _c	Order Number
3.5	32	32	R	2)	50	12.5	0.42 ●	3412.0122.11
3.5	32	32	R	2)	50	12.5	0.42 ●	3412.0122.22
3.5	32	32	R	2)	50	12.5	0.42 ●	3412.0122.24
3.5	32	32	R	2)	50	12.5	0.42 ●	3412.0122.26
4	32	32	S	2)	50	11	0.7 ●	3412.0123.11
4	32	32	S	2)	50	11	0.7 ●	3412.0123.22
4	32	32	S	2)	50	11	0.7 ●	3412.0123.24
4	32	32	S	2)	50	11	0.7 ●	3412.0123.26
5	32	32	T	2)	50	9	1.15 ●	3412.0124.11
5	32	32	T	2)	50	9	1.15 ●	3412.0124.22
5	32	32	T	2)	50	9	1.15 ●	3412.0124.24
5	32	32	T	2)	50	9	1.15 ●	3412.0124.26

Most Popular.

A vailability for all products can be searched real-time: https://www.schurter.com/en/Stock-Check/Stock-Check-SCHURTER

1) 50 A @ 63 VAC, $\cos \phi \ge$ 0.99 / 50 A @ 63 VDC

2) 50 A @ 32 VAC, $\cos \phi \ge$ 0.99 / 50 A @ 32 VDC

Packaging Unit	.xx = .11	100 pcs. in tape in ESD-plastic bag
acc. IEC 60286-3 Type 2a	.xx = .22	1000 pcs. in tape [W: 8mm and P1: 4mm] on reel [A: 18cm]
	.xx = .24	5000 pcs. in tape [W: 8mm and P1: 4mm] on reel [A: 33cm]
	.xx = .26	15000 pcs. in tape [W: 8mm and P1: 4mm] on reel [A: 33cm]

product selected for their own applications.