

## Centre drill HSS, type A, left

For universal use up to 1000 N/mm<sup>2</sup>

**ATORN**<sup>®</sup>



### Application

For centre drilling on conventional and CNC machines.

### Version

- spiral-fluted design with relief grinding. diameter 0.5–0.8, ground on one side

### Advantage

- radial relief ensures optimum chip breaking

Application	Steel (N/mm <sup>2</sup> )			Stainless steel		Alu		Brass		Bronze		Plastics	Graphite G(C)FK	GG(G) GjMW	Titan-alloy	Nickel-alloy	Super-alloy	Hard mat.	
	<700	<1000	<1300	marten.	austen.	short	long	short	long	short	long							<55 HRC	<65 HRC
	35	20	10	10		50	70	40	30	35	30	20	10	20					

<b>Art. No.</b>	<b>11003 400</b>
<b>Countersink angle</b>	60 Degree
<b>Cutting material</b>	HSS
<b>Surface</b>	Uncoated
<b>Form</b>	A
<b>Tool holding device</b>	HA parallel shank
<b>Cutting edge diameter</b>	4.00 mm
<b>Shaft diameter</b>	10 mm
<b>Min./max cutting edge length</b>	5-5.9 mm
<b>Length</b>	55 mm
<b>f steel 700</b>	0.06 mm/U
<b>DIN</b>	333

### EAN-Code

40502934 1500 1