


## EVL-M Assembled adjustable standpipe run tee

EO 24° cone end / Male metric thread – metal sealing edge (ISO 9974)



Pre-assembled, complete with straight male stud connector (with cutting face). Final assembly (in appropriate body) at least 1/4 turn beyond the point of clearly perceptible resistance.

Series	D1 	T	D3	D4	D5	L1	L2	L3	L4	L5	L6	S1	S2	S3	Weight g/1 piece	Order code*	PN (bar) <sup>1)</sup>	
																	CF	71
L <sup>3)</sup>	06	M 10x1.0	4	4	14	19	12.0	34.5	8	23	27	12	14	14	48	<b>EVL06LMOMD</b>	315	315
	08	M 12x1.5	6	6	17	21	14.0	37.5	12	25	29	12	17	17	73	<b>EVL08LMOMD</b>	315	315
	10	M 14x1.5	8	7	19	22	15.0	40.0	12	26	30	14	19	19	89	<b>EVL10LMOMD</b>	315	315
	12	M 16x1.5	10	9	21	24	17.0	43.0	12	27	32	17	22	22	118	<b>EVL12LMOMD</b>	315	315
	15	M 18x1.5	12	11	23	28	21.0	46.0	12	29	36	19	27	24	186	<b>EVL15LMOMD</b>	250	250
	18	M 22x1.5	15	14	27	31	23.5	50.0	14	31	40	24	32	27	269	<b>EVL18LMOMD</b>	250	250
	22	M 26x1.5	19	18	31	35	27.5	55.5	16	33	44	27	36	32	364	<b>EVL22LMOMD</b>	160	160
	28	M 33x2.0	24	23	39	38	30.5	61.0	18	34	47	36	41	41	556	<b>EVL28LMOMD</b>	160	160
	35	M 42x2.0	30	30	49	45	34.5	72.0	20	39	56	41	50	50	900	<b>EVL35LMOMD</b>	160	160
	42	M 48x2.0	36	36	55	51	40.0	79.0	22	42	63	50	60	55	1323	<b>EVL42LMOMD</b>	160	160
S <sup>4)</sup>	06	M 12x1.5	4	4	17	23	16.0	40.0	12	28	31	12	17	17	85	<b>EVL06SMOMD</b>	400	400
	08	M 14x1.5	5	5	19	24	17.0	44.0	12	30	32	14	19	19	119	<b>EVL08SMOMD</b>	400	400
	10	M 16x1.5	7	7	21	25	17.5	47.0	12	31	34	17	22	22	151	<b>EVL10SMOMD</b>	400	400
	12	M 18x1.5	8	8	23	29	21.5	50.0	12	33	38	17	24	24	202	<b>EVL12SMOMD</b>	400	400
	14	M 20x1.5	10	10	25	30	22.0	54.0	14	37	40	19	27	27	264	<b>EVL14SMOMD</b>	400	400
	16	M 22x1.5	12	12	27	33	24.5	56.0	14	37	43	24	30	27	326	<b>EVL16SMOMD</b>	400	400
	20	M 27x2.0	16	16	32	37	26.5	65.0	16	42	48	27	36	32	481	<b>EVL20SMOMD</b>	400	400
	25	M 33x2.0	20	20	39	42	30.0	73.5	18	47	54	36	46	41	904	<b>EVL25SMOMD</b>	250	250
	30	M 42x2.0	25	25	49	49	35.5	80.0	20	50	62	41	50	50	1263	<b>EVL30SMOMD</b>	160	160
	38	M 48x2.0	32	32	55	57	41.0	92.5	22	57	72	50	60	55	1936	<b>EVL38SMOMD</b>	160	160

<sup>1)</sup> Pressure shown = item deliverable

<sup>3)</sup> L = light series; <sup>4)</sup> S = heavy series

$$\frac{PN \text{ (bar)}}{10} = PN \text{ (MPa)}$$

Delivery without nut and ring. Information on ordering complete fittings see page I7.

\*Please add the **suffixes** below according to the material/surface required.

Order code suffixes		
Material	Suffix surface and material	Example
Steel, zinc plated, Cr(VI)-free	CF	EVL16SMOMDCF
Stainless Steel	71	EVL16SMOMD71