



HEADLIGHT CLEANER AND SEALANT

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

Date of issue: 31/10/2018

Revision date:

:

Version: 1.0

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product form : Mixture
Product name : HEADLIGHT CLEANER AND SEALANT
Product code : 15125

1.2. Relevant identified uses of the substance or mixture and uses advised against

1.2.1. Relevant identified uses

Intended for general public
Main use category : Consumer use
Use of the substance/mixture : Automotive Care Products.

1.2.2. Uses advised against

No additional information available

1.3. Details of the supplier of the safety data sheet

Turtle Wax Europe Limited
4th Floor Alaska House, Atlantic Park,
Dunnings Bridge Road
Liverpool, L30 4AB - United Kingdom
T +44 151 530 4740
MSDS@turtlewaxeurope.com

1.4. Emergency telephone number

Emergency number : +44 151 530 4740
Office hours only 08:30 - 17:00

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification according to Regulation (EC) No. 1272/2008 [CLP]

Not classified

2.2. Label elements

Labelling according to Regulation (EC) No. 1272/2008 [CLP]

Precautionary statements (CLP) : P102 - Keep out of reach of children.
EUH-statements : EUH208 - Contains BENZISOTHIAZOLINONE. May produce an allergic reaction.

2.3. Other hazards

Adverse physicochemical, human health and environmental effects : To our knowledge, this product does not present any particular risk, provided it is handled in accordance with good occupational hygiene and safety practice.
Other hazards not contributing to the classification : None under normal conditions.

SECTION 3: Composition/information on ingredients

3.1. Substances

Not applicable

3.2. Mixtures

Name	Product identifier	%	Classification according to Regulation (EC) No. 1272/2008 [CLP]
Distillates (petroleum); hydrotreated light	(CAS-No.) 64742-47-8 (EC-No.) 265-149-8 (EC Index-No.) 649-422-00-2 (REACH-no) 01-2119484819-18	10 - 20	Asp. Tox. 1, H304
APS – ME 355		1 - 10	Skin Irrit. 2, H315 Eye Irrit. 2, H319 STOT SE 3, H335

HEADLIGHT CLEANER AND SEALANT

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

White Mineral Oil (Petroleum)	(CAS-No.) 8042-47-5 (EC-No.) 232-455-8 (REACH-no) 01-2119487078-27	1 - 10	Asp. Tox. 1, H304
-------------------------------	--	--------	-------------------

Full text of H-statements: see section 16

SECTION 4: First aid measures

4.1. Description of first aid measures

First-aid measures general	: If medical advice is needed, have product container or label at hand.
First-aid measures after inhalation	: Not expected to present a significant inhalation hazard under anticipated conditions of normal use. If experiencing respiratory symptoms: Get medical advice/attention.
First-aid measures after skin contact	: Wash skin with soap and water. If skin irritation or rash occurs: Get medical advice/attention.
First-aid measures after eye contact	: Not expected to present a significant eye contact hazard under anticipated conditions of normal use. Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. Seek medical attention if irritation develops.
First-aid measures after ingestion	: Not expected to present a significant ingestion hazard under anticipated conditions of normal use. Rinse mouth. Get medical advice/attention if you feel unwell.

4.2. Most important symptoms and effects, both acute and delayed

Symptoms/effects	: To our knowledge, this product does not present any particular risk, provided it is handled in accordance with good occupational hygiene and safety practice.
Symptoms/effects after inhalation	: Not expected to present a significant inhalation hazard under anticipated conditions of normal use.
Symptoms/effects after skin contact	: May cause an allergic skin reaction.
Symptoms/effects after eye contact	: Not expected to present a significant hazard under anticipated conditions of normal use. May cause slight irritation.
Symptoms/effects after ingestion	: Ingestion may cause nausea and vomiting. May cause a light irritation of the linings of the mouth, throat, and gastrointestinal tract.

4.3. Indication of any immediate medical attention and special treatment needed

Treat symptomatically.

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable extinguishing media	: Use extinguishing media appropriate for surrounding fire.
------------------------------	---

5.2. Special hazards arising from the substance or mixture

Fire hazard	: Not flammable.
Explosion hazard	: Product is not explosive.
Reactivity in case of fire	: Not known.
Hazardous decomposition products in case of fire	: Toxic fumes may be released.

5.3. Advice for firefighters

Precautionary measures fire	: Stop leak if safe to do so.
Firefighting instructions	: Use extinguishing media appropriate for surrounding fire.
Protection during firefighting	: Do not attempt to take action without suitable protective equipment. Self-contained breathing apparatus. Complete protective clothing.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

General measures	: Avoid release to the environment.
------------------	-------------------------------------

6.1.1. For non-emergency personnel

Protective equipment	: Not required for normal conditions of use.
Emergency procedures	: Ventilate spillage area. Stop release. Avoid prolonged or repeated contact with skin.

6.1.2. For emergency responders

Protective equipment	: Not required for normal conditions of use.
Emergency procedures	: Ventilate area. Stop release. Avoid prolonged or repeated contact with skin.

6.2. Environmental precautions

Avoid release to the environment.

6.3. Methods and material for containment and cleaning up

For containment	: Collect spillage.
-----------------	---------------------

HEADLIGHT CLEANER AND SEALANT

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

Methods for cleaning up	: Ventilate spillage area. Wipe up with absorbent material (for example cloth). Place in a suitable container for disposal in accordance with the waste regulations (see Section 13).
Other information	: Dispose in a safe manner in accordance with local/national regulations.

6.4. Reference to other sections

For further information refer to section 8: "Exposure controls/personal protection". For disposal of solid materials or residues refer to section 13 : "Disposal considerations".

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Precautions for safe handling	: Observe the label precautions. Ensure adequate ventilation. Keep out of reach of children. Avoid prolonged or repeated contact with skin.
Hygiene measures	: Always wash hands after handling the product. Do not eat, drink or smoke when using this product.

7.2. Conditions for safe storage, including any incompatibilities

Storage conditions	: Store in a well-ventilated place. Keep cool. Keep out of reach of children. Keep container closed when not in use.
Incompatible products	: Strong acids.
Incompatible materials	: None known.
Storage area	: Store in a well-ventilated place. Keep out of frost.

7.3. Specific end use(s)

Automotive Care Products.

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

No additional information available

8.2. Exposure controls

Appropriate engineering controls	: Ensure adequate ventilation.
Personal protective equipment	: In case of repeated or prolonged contact wear gloves.
Materials for protective clothing	: Not required for normal conditions of use
Hand protection	: In case of repeated or prolonged contact wear gloves
Eye protection	: Eye protection should only be necessary where liquid could be splashed or sprayed
Skin and body protection	: Not required for normal conditions of use
Respiratory protection	: Not necessary with sufficient ventilation
Environmental exposure controls	: Avoid release to the environment.
Consumer exposure controls	: Read label before use. Observe the label precautions.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Physical state	: Liquid
Colour	: No data available
Odour	: characteristic.
Odour threshold	: No data available
pH	: No data available
Relative evaporation rate (butylacetate=1)	: No data available
Melting point	: Not applicable
Freezing point	: No data available
Boiling point	: No data available
Flash point	: > °C
Auto-ignition temperature	: No data available
Decomposition temperature	: No data available
Flammability (solid, gas)	: Not applicable
Vapour pressure	: No data available
Relative vapour density at 20 °C	: No data available
Relative density	: No data available
Solubility	: No data available

HEADLIGHT CLEANER AND SEALANT

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

Log Pow	: No data available
Viscosity, kinematic	: 115 cSt
Viscosity, dynamic	: 115 cP
Explosive properties	: Product is not explosive.
Oxidising properties	: Non oxidizing.
Explosive limits	: No data available

9.2. Other information

No additional information available

SECTION 10: Stability and reactivity

10.1. Reactivity

The product is non-reactive under normal conditions of use, storage and transport.

10.2. Chemical stability

Stable under normal conditions.

10.3. Possibility of hazardous reactions

No dangerous reactions known under normal conditions of use.

10.4. Conditions to avoid

None under recommended storage and handling conditions (see section 7).

10.5. Incompatible materials

Strong acids. Oxidizing agent.

10.6. Hazardous decomposition products

Under normal conditions of storage and use, hazardous decomposition products should not be produced.

SECTION 11: Toxicological information

11.1. Information on toxicological effects

Acute toxicity : Not classified

Distillates (petroleum); hydrotreated light (64742-47-8)	
LD50 oral	> 5000 mg/kg bodyweight
LD50 dermal	> 2000 mg/kg bodyweight
LC50 inhalation rat (Dust/Mist - mg/l/4h)	> 5280 mg/l/4h

Skin corrosion/irritation	: Not classified
Serious eye damage/irritation	: Not classified
Respiratory or skin sensitisation	: Not classified
Germ cell mutagenicity	: Not classified
Carcinogenicity	: Not classified
Reproductive toxicity	: Not classified
STOT-single exposure	: Not classified
STOT-repeated exposure	: Not classified
Aspiration hazard	: Not classified

HEADLIGHT CLEANER AND SEALANT	
Viscosity, kinematic	115 mm ² /s

SECTION 12: Ecological information

12.1. Toxicity

Ecology - general : The product is not considered harmful to aquatic organisms nor to cause long-term adverse effects in the environment.

Ecology - water : No data available on ecotoxicity.

Distillates (petroleum); hydrotreated light (64742-47-8)	
LC50 fish 1	> 2 mg/l

12.2. Persistence and degradability

HEADLIGHT CLEANER AND SEALANT	
Persistence and degradability	No data available.

HEADLIGHT CLEANER AND SEALANT

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

12.3. Bioaccumulative potential

HEADLIGHT CLEANER AND SEALANT

Bioaccumulative potential	No data available.
---------------------------	--------------------

12.4. Mobility in soil

HEADLIGHT CLEANER AND SEALANT

Ecology - soil	No data available.
----------------	--------------------

12.5. Results of PBT and vPvB assessment

No additional information available

12.6. Other adverse effects

Other adverse effects : None known.
Additional information : Avoid release to the environment.

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Regional legislation (waste) : Disposal must be done according to official regulations.
Waste treatment methods : Dispose of contents/container in accordance with licensed collector's sorting instructions.
Product/Packaging disposal recommendations : Dispose in a safe manner in accordance with local/national regulations.

SECTION 14: Transport information

In accordance with ADR / RID / IMDG / IATA / ADN

ADR	IMDG	IATA	ADN	RID
14.1. UN number				
Not regulated for transport				
14.2. UN proper shipping name				
Not applicable	Not applicable	Not applicable	Not applicable	Not applicable
14.3. Transport hazard class(es)				
Not applicable	Not applicable	Not applicable	Not applicable	Not applicable
Not applicable	Not applicable	Not applicable	Not applicable	Not applicable
14.4. Packing group				
Not applicable	Not applicable	Not applicable	Not applicable	Not applicable
14.5. Environmental hazards				
Dangerous for the environment : No	Dangerous for the environment : No Marine pollutant : No	Dangerous for the environment : No	Dangerous for the environment : No	Dangerous for the environment : No
No supplementary information available				

14.6. Special precautions for user

- Overland transport

No data available

- Transport by sea

No data available

- Air transport

No data available

- Inland waterway transport

Carriage prohibited (ADN) : No

Not subject to ADN : No

- Rail transport

Carriage prohibited (RID) : No

14.7. Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code

Not applicable

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

15.1.1. EU-Regulations

HEADLIGHT CLEANER AND SEALANT

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

Contains no REACH substances with Annex XVII restrictions

Contains no substance on the REACH candidate list

Contains no REACH Annex XIV substances

Detergent Regulation : Ingredient data sheet:

Component	CAS-No.	%
AQUA	7732-18-5	>=10%
Nepheline syenite	37244-96-5	>=10%
C13-14 ALKANE	64742-47-8	>=10%
APS – ME 355		1 - 10%
White Mineral Oil	8042-47-5	1 - 10%
Morpholine oleate	1095-66-5	1 - 10%
GLYCERIN	56-81-5	0.1 - 1%
DIPROPYLENE GLYCOL	25265-71-8	0.1 - 1%
Tributhoxyethylphosphate	78-51-3	<0.1%
PPG-2 METHYL ETHER	34590-94-8	<0.1%
BENZISOTHIAZOLINONE	2634-33-5	<0.1%
SODIUM HYDROXIDE	1310-73-2	<0.1%
C9-11 PARETH-6	68439-46-3	<0.1%
CYCLOHEXANE	110-82-7	<0.1%

Detergent Regulation : Labelling of contents:

Component	%
BENZISOTHIAZOLINONE	

15.1.2. National regulations

In accordance with EU Directive 1272/2008/EC Annex VI (2.2.5) this product will not sustain combustion and is not regarded as requiring a flammable warning.

15.2. Chemical safety assessment

No chemical safety assessment has been carried out

SECTION 16: Other information

Indication of changes:

Transport information.

Full text of H- and EUH-statements:

Asp. Tox. 1	Aspiration hazard, Category 1
Eye Irrit. 2	Serious eye damage/eye irritation, Category 2
Skin Irrit. 2	Skin corrosion/irritation, Category 2
STOT SE 3	Specific target organ toxicity — Single exposure, Category 3, Respiratory tract irritation
H304	May be fatal if swallowed and enters airways.
H315	Causes skin irritation.
H319	Causes serious eye irritation.
H335	May cause respiratory irritation.
EUH208	Contains BENZISOTHIAZOLINONE. May produce an allergic reaction.

SDS EU TURTLEWAX

This information is based on our current knowledge and is intended to describe the product for the purposes of health, safety and environmental requirements only. It should not therefore be construed as guaranteeing any specific property of the product