

## Micrometer

Interchangeable anvil

Mitutoyo

### Application:

For measuring e.g. shank diameters, external dimensions of workpieces etc.

### Execution:

- Semi-gloss chrome-plated scale drum and sleeve
- Carbide-tipped measuring faces
- Friction coupling for consistent, repeatable measuring force

### Advantage:

- With interchangeable measuring anvil for a variable measuring range

### Delivery:

Includes box, setting standard, measuring inserts, adjustment wrench



<b>Art. no.</b>	<b>32016 150</b>
<b>Brand</b>	MITUTOYO
<b>Manufacturer Part Number</b>	104-142A
<b>Min./max. length measuring range</b>	300-400 mm
<b>Vernier scale</b>	0.01 mm
<b>Measuring surface diameter</b>	8 mm
<b>Measuring spindle increments</b>	0.5 mm
<b>Spindle clamping</b>	Yes
<b>Display</b>	Nonius
<b>Number of setting dimensions</b>	4 PCS
<b>Number of pieces</b>	8 PCS
<b>Min./max. measurement force</b>	10-14 N
<b>Calibration Group</b>	D
<b>Gross Weight</b>	5.500 kg
<b>Product Group</b>	3MA

### EAN

4946368215143

