

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0348250125**
Status: **Active**
Overview: [Mini50 Connection Systems](#)
Description: Mini50 Unsealed Vertical Header, Dual Row, 12 Circuit, Polarization Option B, Gray, Tray

Documents:

| | |
|---|---|
| 3D Model | Application Specification AS-34791-020-FR-001 (PDF) |
| Drawing (PDF) | Packaging Specification PK-31301-440-001 (PDF) |
| 3D Model (PDF) | Test Summary 347910020-TS-000 (PDF) |
| Product Specification PS-34791-020-001 (PDF) | Datasheet (PDF) |
| Application Specification AS-34791-020-001 (PDF) | RoHS Certificate of Compliance (PDF) |
| Application Specification AS-34791-020-CH-001 (PDF) | |

General


| | |
|----------------|---|
| Product Family | PCB Headers |
| Series | 34825 |
| Application | Automotive, Power, Signal, Wire-to-Board |
| Overview | Mini50 Connection Systems |
| Product Name | Mini50 |
| UPC | 887191338675 |

Physical

| | |
|--------------------------------|--------------------------------|
| Breakaway | No |
| Circuits (Loaded) | 12 |
| Circuits (maximum) | 12 |
| Color - Resin | Gray |
| Durability (mating cycles max) | 10 |
| First Mate / Last Break | No |
| Glow-Wire Capable | No |
| Guide to Mating Part | No |
| Keying to Mating Part | Yes |
| Lock to Mating Part | Yes |
| Material - Metal | Brass |
| Material - Plating Mating | Tin |
| Material - Plating Termination | Tin |
| Material - Resin | High Temperature Thermoplastic |
| Net Weight | 2.068/g |
| Number of Rows | 2 |
| Orientation | Vertical |
| PC Tail Length | 2.87mm |
| PCB Locator | Yes |
| Packaging Type | Tray |
| Pitch - Mating Interface | 2.00mm |
| Plating min - Mating | 2.500µm |
| Plating min - Termination | 2.500µm |
| Polarized to Mating Part | Yes |
| Polarized to PCB | Yes |
| Temperature Range - Operating | -40° to +105°C |
| Termination Interface: Style | Through Hole |

Electrical

| | |
|-------------------------------|---------------------------|
| Current - Maximum per Contact | 4.0A (for reference only) |
| Voltage - Maximum | 14V (typical operating) |



EU ELV
Compliant

EU RoHS
Compliant
REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free
Status

Low-Halogen

For more information, please visit [Contact US](#)

| | |
|-----------------|---------------|
| China ROHS | Not Relevant |
| ELV | Compliant |
| RoHS Phthalates | Not Contained |

China RoHS

Search Parts in this Series

[34825 Series](#)

Mates With

[34824 Mini50 Unsealed Dual Row Receptacle](#)

Solder Process Data

Lead-free Process Capability

N/A

Material Info**Reference - Drawing Numbers**

Application Specification

AS-34791-020-001, AS-34791-020-CH-001,
AS-34791-020-FR-001

Packaging Specification

PK-31301-440-001

Product Specification

PS-34791-020-001

Sales Drawing

SD-34825-001-001

Test Summary

347910020-TS-000

This document was generated on 02/01/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION