



KGC-310M-C



Performance enhanced!
Function enhanced!



Managed 10/100/1000Base-T to Dual-speed Fiber Media Converters

Product Highlights:

- Tri-speed copper to dual-speed fiber conversion
- Fiber link loop back test
- Remote Copper link monitoring
- Optional DIN-Rail mounting
- Center Chassis support
- Web & SNMP management
- 802.1Q Control
 - Packet type filtering
 - Packet VID filtering
 - 802.1Q tag stripping
 - 802.1Q tagging
 - 802.1ad Q-in-Q support
 - 802.1ad S-tag tagging

DIN-Rail Mounting Bracket
KC-3DR



Center Chassis



Key Features:

- Tri-speed 10/100/1000Mbps copper to dual-speed 1G/100Mbps fiber conversion
- Comply with IEEE 802.3, 802.3u, 802.3ab, 802.3z standard
- Support full wire speed conversion for Gigabit copper to Gigabit fiber
- Support auto-negotiation with link partners
- Provide dual-speed SFP on fiber port for mounting variety of fiber options
- Provide loop back test function with link partner over fiber link
- Provide monitoring function for remote link partner's copper link status
- Provide important LFPT (Link Fault Pass Through) media converter function
- Support optional DIN-Rail installation
- Support center chassis installation to achieve the advantages of central power, optional power redundancy and network management
- Ideal solution for multimode, short reach up to long reach single mode fiber, Bi-Di applications
- Web-based configuration management support
- Support SNMP management
- Port operating mode, flow control and status monitoring functions
- Tagged or untagged packet filtering
- 802.1Q VLAN tag stripping and tagging
- Support Provider bridging (VLAN Q-in-Q) application with double tag capability
- Support S-tag ethernet type tagging
- Support Jumbo frame conversion
- LLDP support
- Energy efficient ethernet (EEE) support

Specifications:

Standard	IEEE 802.3, 802.3u, 802.3ab, 802.3z, 802.1ad, 802.3az, 802.1Q
Copper Port	Shielded RJ-45, 10/100/1000Mbps, Full/Half duplex Auto-negotiation, Auto-MDI/MDI-X
Fiber Port	SFP connector with pre-configured SFP fiber transceiver 1G/100Mbps Full duplex, Auto-negotiation Far End Fault support
Network Cables	Copper port: Cat.5e recommended or higher up to 100m Fiber port: MMF 50/125µm, 62.5/125µm, SMF 9/125µm
DIP Switches	Copper port operating mode Flow control Auto report for remote copper link status
LED Indication	Power status Local copper port status - link, speed, duplex Local fiber port link status Remote copper port status - link, speed, duplex Loop back test status
Jumbo Frame size	Support 9600 bytes max.



Ordering Information:

KGC-310M-C

Model	Fiber		Distance
-	No SFP Transceiver		
-SX	LC	850	50/125 62.5/125 500m 200m
-LX	LC	1310	MMF SMF 550m 10km
-LX20	LC	1310	SMF 20km
-LX30	LC	1310	SMF 30km
-LX50	LC	1550	SMF 50km
-LX70	LC	1550	SMF 70km
-W3510	LC	Tx1310 Rx1550	Bi-Di SMF 10km
-W5310	LC	Tx1550 Rx1310	Bi-Di SMF 10km
-W3520	LC	Tx1310 Rx1550	Bi-Di SMF 20km
-W5320	LC	Tx1550 Rx1310	Bi-Di SMF 20km
-W3410	LC	Tx1310 Rx1490	Bi-Di SMF 10km
-W4310	LC	Tx1490 Rx1310	Bi-Di SMF 10km
-W3410S	SC	Tx1310 Rx1490	Bi-Di SMF 10km
-W4310S	SC	Tx1490 Rx1310	Bi-Di SMF 10km

KC-3DR	DIN-Rail mounting bracket
KC-1300	Managed center chassis

Loop Back Test	Push button to start remote loop-back test with link partner over fiber link
Mounting	Desktop, Wall, DIN-Rail (optional), Center chassis
Center Chassis	Up to 16 units in one rack chassis with central power Support optional power redundancy and management
Power Input	+5 ~ +12VDC (+/-5%) Consumption 4.2W max. @5V Less than 3.5W when no link ports under power saving mode
Environment	Operating Temperature: -40°C ~ 70°C (Main device) 0°C ~ 40°C (External power adapter) Storage Temperature: -40°C ~ 85°C Relative Humidity: 5% ~ 95% non-condensing
Dimension	72.5 x 108 x 23 mm (WxDxH)
Approval	FCC Class A, CE mark Class A, VCCI Class A, C-Tick

Management:

Management	Web-based browser interface, SNMP manager
Port Control	Operating mode, Flow control
Packet Filtering	802.1Q tagged packet filtering, Untagged packet filtering
802.1Q VLAN	Ingress 802.1Q tag stripping, Egress 802.1Q tagging (tag insertion) S-tag tagging (802.1ad double tagging)
Monitoring	Local Port status, Remote Port status, Port statistics
Maintenance	Restore factory default, reboot, firmware update
SNMP Trap	Trap events: Boot up, Login failure, Copper port link change, Fiber port link change
Power saving	Disable, Link Up, Link Down, Full

Fiber Optical Specifications:

Model	Fiber Port	Wavelength	Tx Power*	Rx Sens.	Rx Max.
-SX	LC MMF	850nm	-9.5 ~ -4dBm	-18dBm	0Bm
-LX	LC SMF	1310nm	-9.5 ~ -3dBm	-20dBm	-3dBm
-LX20	LC SMF	1310nm	-8 ~ -2dBm	-23dBm	-1dBm
-LX30	LC SMF	1310nm	-4 ~ +1dBm	-24dBm	-3dBm
-LX50	LC SMF	1550nm	-4 ~ +1dBm	-24dBm	-3dBm
-LX70	LC SMF	1550nm	0 ~ +5dBm	-24dBm	-3dBm
-W3510	Bi-Di LC SMF	Tx 1310nm Rx 1550nm	-9 ~ -3dBm	-21dBm	-1dBm
-W5310	Bi-Di LC SMF	Tx 1550nm Rx 1310nm	-9 ~ -3dBm	-21dBm	-1dBm
-W3520	Bi-Di LC SMF	Tx 1310nm Rx 1550nm	-8 ~ -2dBm	-23dBm	-1dBm
-W5320	Bi-Di LC SMF	Tx 1550nm Rx 1310nm	-8 ~ -2dBm	-23dBm	-1dBm
-W3410	Bi-Di LC SMF	Tx 1310nm Rx 1490nm	-9 ~ -3dBm	-21dBm	-1dBm
-W4310	Bi-Di LC SMF	Tx 1490nm Rx 1310nm	-9 ~ -3dBm	-21dBm	-1dBm
-W3410S	Bi-Di SC SMF	Tx 1310nm Rx 1490nm	-9 ~ -3dBm	-21dBm	-1dBm
-W4310S	Bi-Di SC SMF	Tx 1490nm Rx 1310nm	-9 ~ -3dBm	-21dBm	-1dBm

*Data for 62.5/125µm MMF, 9 /125µm SMF



Katron Technologies Inc.
15F-7, No. 79, Sec. 1, Hsin Tai Wu Rd.,
Hsi-chih District, New Taipei City, Taiwan
Tel: 886-2-2698-3878
Fax: 886-2-2698-3873
E-mail: kti@ktinet.com.tw
URL: http://www.ktinet.com.tw

Trademarks: All brand names are trademarks or registered trademarks of their respective holders.
This information is subject to change without prior notice.