

TY27MX



CABLE TIE 120LB 13IN UV BLK NYLON



General Information

Extended Product Type	TY27MX
Product ID	7TAG009320R0004
EAN	5414363063407
Catalog Description	CABLE TIE 120LB 13IN UV BLK NYLON
Long Description	High Performance Cable Tie, Weather and Ultraviolet Resistant for Indoor and Outdoor Applications, Black Color Nylon 6.6, Length of 340mm (13.4 Inches) for Bundle Diameter up to 102mm (4 Inches), Width of 6.9mm (0.271 Inch), Tensile Strength Rating of 534 Newtons (120 Pounds), Operating Temperature of -60 Degrees Celsius (-76 F) to 85 Degrees Celsius (185 F), Bulk Pack

Ordering

EAN	5414363063407
Customs Tariff Number	3926909990

Dimensions

Product Net Weight	.01 lb 4.535 g
--------------------	-------------------

Container Information

Package Level 1 Units	500 piece
Package Level 1 Width	14 in 356 mm
Package Level 1 Depth / Length	22 in 559 mm
Package Level 2 Units	1000 piece
Package Level 2 Width	5 in 127 mm
Package Level 2 Height	9.5 in 241 mm
Package Level 2 Depth / Length	15.25 in 387 mm

Additional Information

Brand / Label	Ty-Rap
Bundle Diameter	0.236 to 3.54 in 6 to 90 mm

Color	Black
Lock Type	Stainless Steel Barb
Material	Nylon/Polyamide 6.6
Number of Batteries	0
Product Name	PLASTIC CABLE TIE
Product Type	Standard
Special Functions	Low profile head is designed to prevent snags on uneven surfaces and easier to pull through bulkheads. Non-magnetic stainless steel locking device insures both maximum strength and the right tightness every time.
Standards	UL E49405
Surface Finishing	Untreated
Tensile Strength	120 lb 530 N
Thickness	0.06 in 1.65 mm
UPC	786210824789

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	TY27MX
Instructions and Manuals	TY27MX

Classifications

ETIM 6	EC000046 - Cable tie
ETIM 7	EC000046 - Cable tie
UNSPSC	39121703
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5034 >> Cable ties

Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Cable Ties

