

305183 ✓ ACTIVE

AMP | AMP Type II, AMP Type III+

TE Internal #: 305183

AMP Type II, Insertion & Extraction Tools, Contact Extraction,
Contact-to-Housing

[View on TE.com >](#)



Application Tooling > Insertion & Extraction Tools



Insertion & Extraction Tool Type: **Contact Extraction**

Insertion & Extraction Tool Application: **Contact-to-Housing**

Features

Product Type Features

Insertion & Extraction Tool Type	Contact Extraction
Insertion & Extraction Tool Application	Contact-to-Housing

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2022 (223) Candidate List Declared Against: JUL 2021 (219) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous

materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CAT-AM71-T98
TYPE II CONTACTS



TE Part # CAT-AM71-T98D
TYPE III CONTACTS LP EMEA



TE Part # CAT-AM71-T98E
TYPE III CONTACTS LP



TE Part # CAT-AM71-T98A
TYPE III CONTACTS LP



TE Part # CAT-AM71-T98G
TYPE III CONTACTS LP HIGH CURRENT



TE Part # CAT-AM71-T98B
TYPE III CONTACTS STRIP



TE Part # CAT-AM71-T98F
TYPE III CONTACTS STRIP HIGH CURRENT



TE Part # CAT-AM71-T98C
TYPE III CONTACTS STRIP EMEA



TE Part # 66361-1
III+ PIN,18-14,30AU>10,LP



TE Part # 193846-1
SKT ASSY.



TE Part # 66099-1
III+ PIN,18-16,30AU>10,LP



TE Part # 1-66105-8
III+ SKT,24-20,30AU/FL,SMPACK



TE Part # 66105-2
III+ SKT,24-20,TIN-LEAD,LP



TE Part # 66103-1
III+ PIN,24-20,30AU>10,LP





TE Part # 66358-6
III+ SKT,18-14,TIN-LEAD,STRIP





TE Part # 66101-2
III+ SKT,18-16,TIN-LEAD,LP



Also in the Series | AMP Type II





Also in the Series | AMP Type III+



Customers Also Bought





Documents

Product Drawings

[EXTRACT TOOL TYPE 2 20-16](#)

English

Product Environmental Compliance

[MD_305183_112320122240](#)

English

[MD_305183_112320122240](#)

English

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English

Agency Approvals

[CSA Certificate](#)

English