

Part Number: BE43769

RailTuff Cat 5e, PROFINET, AWG 22 (19)



[Request Sample](#)

Product Description

RailTuff Railway Approved Cat 5e, PROFINET, AWG 22(19), HiFlex, Premium Cross-linked LSNH Insulation and Jacket, Heavy Shielded, DIN 5510-2 level 1 to 4, EN 50155 Flame Resistance acc EN/TS 45545, IEC 60332-1-2, EN 50305 & IEC 60332-3-25 cat D, EN/TS 45545 (Class R15 and R16 HL3), Oil Resistance

Technical Specifications

Product Overview

Environmental Space:	Indoor
Suitable Applications:	For use in railway applications such as rolling stock, buses or other vehicles, cable meets the requirements of the relevant part of international railway standards like DIN 5510-2, EN 50153, EN 50155, EN 50305 and CEN/TS 45545

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	Construction n x D	No. of Conductors
22	Stranded	TC - Tinned Copper	19x0.15 mm	4

Conductor, Table Note:	IEC 60228 class 5
Conductor Count:	4
Total Number of Pairs:	2
Conductor Size:	22 AWG

Insulation

Material	Nominal Diameter	Diameter +/- Tolerance
PO - Polyolefin	1.63 mm	0.05 mm

Color Chart

Number	Color
Quad 1	White & Blue & Yellow & Orange

Inner Jacket Material

Material	Nominal Diameter
FRNC / LSZH Bedding	4.3 mm

Outer Shield Material

Type	Material	Thickness of Foil	Min. Coverage [%]
Tape	Aluminum/Polyester	50 / 23 µm	
Braid	TC - Tinned Copper		80 %

Outer Jacket Material

Material	Color	Nominal Diameter	Diameter +/- Tolerance	Min. Wall Thickness
Cross-linked LSZH / FRNC	Black	6.7 mm	0.3 mm	0.8 mm

Construction and Dimensions

Cabling

Description
1 quad with center filler

Electrical Characteristics

Conductor DCR

Max. Conductor DCR

57.1 Ohm/km

Shielding: SF/UTP - Overall Braid + Foil

Impedance

Frequency [MHz]	Nominal Characteristic Impedance	Nominal Characteristic Tolerance
1 - 100	100 Ohm	15 Ohm

Delay

Max. Delay	Nominal Velocity of Propagation (VP) [%]
530 ns/100m	66 %

High Freq

Frequency [MHz]	Max. Insertion Loss (Attenuation)	Min. NEXT [dB]	Min. FEXT
1 MHz	2.1 dB/100m	65.3 dB	64 dB
4 MHz	4.1 dB/100m	56.3 dB	52 dB
10 MHz	6.5 dB/100m	50 dB	43.8 dB
16 MHz	8.3 dB/100m	47 dB	40 dB
31.25 MHz	11.7 dB/100m	42.9 dB	33.9 dB
62.5 MHz	17 dB/100m	38.4 dB	28 dB
100 MHz	22 dB/100m	35.3 dB	24 dB

Transfer Impedance

Frequency [MHz]	Transfer Impedance
10 Mhz	Max. 10 mOhm/m

Voltage

Voltage Rating [V]

300 V

Temperature Range

Installation Temp Range:	-5°C To +50°C
Storage Temp Range:	-40°C To +90°C
Operating Temp Range:	-40°C To +90°C

Mechanical Characteristics

Oil Resistance:	IEC 60811-2-1
Bulk Cable Weight:	68 kg/km
Min Bend Radius (W/o Pulling Strength):	67 mm
Min Setting Radius:	33.5 mm
No Adherence Wire to Wire/Wire to Jacket:	No adherence

Standards

CENELEC Compliance:	EN 50153, EN 50155 and EN 50305
Data Category:	Category 5e
Other Specification:	EN 50306 par 4.8 + 4.9 + 4.10 (1.5 kV/1min); Toxicity index to NF X70-100 CITc Max. 0.7 CEN/TS 45545 (Class R14 HL 3)

Applicable Environmental and Other Programs

EU RoHS Compliance Date (yyyy-mm-dd):	2004-01-01
---------------------------------------	------------

Flammability, LSOH, Toxicity Testing

ISO/IEC Flammability:	IEC 60332-1-2 and IEC 60332-3-25
Fire Resistance (CI, Time to Failure):	DIN 5510-2 protection level 1 to 4
Other Flammability:	DIN 5510 protection level 1 to 4 ; EN 50305
Amount of Halogen acc. to IEC 60754-1 & EN50267-1:	Zero

Part Number

Variants

Item #	Color
BE43769.00305	Black
BE43769.00500	Black

Patent: <https://www.belden.com/resources/patents>

History

Revision Number: 5

© 2018 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.