

Hydro-expansion chuck ISO 7388-1

Short slim design, type AD/AF

ATORN

Application:

For clamping drill bits and milling tools with straight shank.

Version:

- High clamping forces
- Axial longitudinal adjustment
- Highly precise centric clamping
- Outstanding absorption
- Standard tool changes as with expansion chucks without requiring additional devices
- Various applications when used with reducer bushings
- With Balluff chip hole
- Can be clamped with all common shank types

Advantage:

- High degree of torque transmission
- Good surface qualities
- Suitable for high rotation speeds
- Excellent vibration-absorbing properties
- Longer service life of cutting tools

Delivery:

Tool holder with matching hex key



Art. no.	23333 466
Tool holding device	SK 50
Clamping diameter	18 mm
Projecting length	80.5 mm
Form	AD/AF
Outer diameter	49.5 mm
Tapered diameter	40 mm
Clamp in depth	46 mm
Max. adjustment travel	10 mm
Coolant supply	Yes
Suitable for thread	M12 x 1
Width across flats	5 mm
Balancing quality	G 2.5 at 25 rpm
Concentricity tolerance	0.003 mm

EAN-Code

4050293151046