


## Data Sheet

**Type Number** ..... 301  
**Designation IEC** ..... SR 43  
**System** ..... Silver oxide / Zinc /  
 NaOH - Electrolyte



**Nominal Voltage** ..... 1,55 V  
**Typical Capacity C** ..... 115 mAh  
 Load 5,6 kOhm, at 20°C down to 1.2 V

**Weight (approx.)** ..... 1,78 g  
**Volume** ..... 0,39 ccm  
**Coding**..... Date of Manufacturing  
 Month/Year

**Temperature Ranges** min max.  
 Storage ..... -10°C 65°C  
 Discharge ..... -10°C 65°C

**Dimensions** min max.  
 Diameter (Ø)..... 11,25 11,6  
 Height (A/B) ..... 3,8 4,2

**Segment** ..... Watch

**Main Applications** ..... Watch  
 Photo  
 Electronic

### Typical Capacities (at 20 °C)

| Discharge Type                            | Load              | End Voltage:    | 1.2 V |
|---|-------------------|-----------------|-------|
| Continuous<br>24h/d,7d/w<br>Current [µA]: | 5600 Ω<br><br>275 | Time:           | 420 h |
|   |                   | Capacity [mAh]: | 115   |
|   |                   | Energy [mWh]:   | 180   |