

Vertical cabinets with easy-view storage bins, two rows

With 3 or 5 vertical pull-out drawers



Execution:

- Robust design made of 3 mm steel sheet
- Sturdy plastic rollers with needle bearings that withstand heavy loads
- Lockable drawers with labelling space
- Load capacity per drawer 900 kg (option up to 1800 kg on request)
- Can be easily moved by pallet truck when empty
- Solidly manufactured storage trays made of 1.5 mm galvanised steel sheet, each with 16 easy-view storage bins L x W x H 160 x 105 x 75 mm
- Other colours deliverable on request

Advantage:

- Double storage enables work based on the Kanban principle
- Clearly visible storage of up to 800 products by type



Art. no.	50049 021
Brand	APFEL
Manufacturer Part Number	2331258
Model	WK 002 set L plus
Door design	Full-sheet panel
Number of vertical pull-out mechanisms	5 PCS
Vertical pull-out mechanism design	800 clear storage bins, set up in two rows
Load-carrying capacity per pull-out mechanism	900 kg
Height	2140 mm
Width	1040 mm
Depth	1050 mm
Load-carrying capacity	4500 kg
Lock type	Cylinder lock
Material	Sheet steel
Cabinet colour	Gentian blue RAL 5010
Colour of front	Grey white RAL 9002
Surface	Powder-coated
Gross Weight	550.000 kg
Product Group	586