

Bit set Standard 25 mm



Order-No.		
32055	⊕ 10 x PH1	10
07855	⊕ 3 x PH1	10
36275	⊕ 20 x PH2	10
24733	⊕ 10 x PH2	10
07856	⊕ 3 x PH2	10
36280	⊕ 10 x PH3	10
07857	⊕ 3 x PH3	10
07858	1 x PH1 ⊕ 1 x PH2 1 x PH3	10
35709	⊕ 20 x PZ1	10
32070	⊕ 10 x PZ1	10
07859	⊕ 3 x PZ1	10
36282	⊕ 20 x PZ2	10
24742	⊕ 10 x PZ2	10
07860	⊕ 3 x PZ2	10
32071	⊕ 10 x PZ3	10
07861	⊕ 3 x PZ3	10
20542	⊕ 1 x PZ4	10
07862	1 x PZ1 ⊕ 1 x PZ2 1 x PZ3	10
35832	⊗ 10 x T10	10
08421	⊗ 2 x T10	10
34746	⊗ 10 x T15	10
08422	⊗ 2 x T15	10
24746	⊗ 10 x T20	10
08423	⊗ 2 x T20	10
08424	⊗ 2 x T25	10
24748	⊗ 10 x T25	10
26451	⊗ 2 x T27	10
08425	⊗ 2 x T30	10
08426	⊗ 2 x T40	10
36288	⊗ 10 x T40	10
38649	⊗ 2 x T10H	10
38650	⊗ 2 x T15H	10
38651	⊗ 2 x T20H	10

38652	⊗ 2 x T25H	10
38653	⊗ 2 x T30H	10
38654	⊗ 2 x T40H	10
22651	1 x 2,0 ⊗ 1 x 2,5 1 x 3,0	10
22653	1 x 3,0 ⊗ 1 x 4,0 1 x 5,0	10
22655	1 x 4,0 ⊗ 1 x 5,0 1 x 6,0	10
07865	1 x 2,0 ⊗ 1 x 2,5 1 x 3,0	10
07866	1 x 4,0 ⊗ 1 x 5,0 1 x 6,0	10
38656	⊗ 2 x 3,0	10
25681	⊗ 2 x 4,0	10
25679	⊗ 2 x 5,0	10
38657	⊗ 2 x 6,0	10
38658	⊗ 2 x #1 x 2,3	10
38659	⊗ 2 x #2 x 2,8	10
38660	⊗ 2 x #3 x 3,3	10
38661	1 x #1 x 2,3 ⊗ 2 x #2 x 2,8 3 x #3 x 3,3	10

Standard bit reduced diameter: 25 mm



Order-No.		
35834	⊕ 10 x PH2	10
36285	⊕ 10 x PZ2	10