
KEMET Part Number: ALF20C103EC063



ALF20, Aluminum Electrolytic, 85C, 10,000 uF, 20%, 63 VDC, -40/+85C



Dimensions		
D	40mm +1mm	
L	35mm +/-2mm	
S	22.5mm +/-0.1mm	
LL	5.5mm +/-1mm	
F	1.486mm +/-0.076mm	

Packaging Specifications		
Weight:	57 g	
Packaging:	Bulk	
Packaging Quantity:	72	

General Information		
Supplier:	KEMET	
Series:	ALF20	
Dielectric:	Aluminum Electrolytic	
Style:	Press-Fit	
Description:	Press-Fit, Aluminum Electrolytic	
RoHS:	Yes	
Lead:	4 Pin Press-Fit	
Notes:	Dimensions Include Sleeving	
Shelf Life:	156 Weeks	

Specifications		
Capacitance:	10,000 uF	
Capacitance Tolerance:	20%	
Voltage DC:	63 VDC, 72.5 VDC (Surge)	
Temperature Range:	-40/+85C	
Rated Temperature:	85C	
Life:	18000 Hrs (Rated Voltage And Ripple Current At 85C), 29000 Hrs (Rated Voltage at 85C)	
Resistance:	80 mOhms (100Hz 20C), 72 mOhms (10kHz 20C)	
Ripple Current:	4.58 Amps (100Hz 85C), 4.67 Amps (10kHz 85C)	
Leakage Current:	3780 uA (5min 20C)	

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

