
TTI

TG120 Low-cost 20MHz Function Generator



- 0.2Hz to 20MHz frequency range
- 10mV to 20V pk-pk from 50 Ω
- TTL/CMOS auxilliary output
- DC offset control with zero detent
- Variable symmetry control
- External sweep input

An essential instrument

The function generator is one of the most versatile instruments available.

It can generate a variety of precision waveshapes over a range of frequencies from mHz to MHz. It can provide a wide range of controlled amplitudes from a low impedance source and maintain constant amplitude as the frequency is varied.

Voltage control of frequency allows FM modulation to be introduced or can provide a swept frequency source for such tasks as frequency response testing.

20MHz from a low-cost generator

Most lower cost function generators use a technology which enables them to operate up to no more than 2MHz.

The TG120 utilises an alternative technology which retains its waveform quality right up to 20MHz.

Variable symmetry for pulse and ramp waveforms

The TG120 provides switchable bi-directional variable symmetry which enables variable duty cycle pulse waveforms and sawtooths to be generated.

Sweep mode operation (external)

The TG120 can be operated in sweep mode by connecting an external sweep voltage. A sweep range of at least 20:1 can be achieved.

Wide range level control

The TG120 provides a main output with a maximum emf of 20V pk-pk from a 50Ω source.

An amplitude vernier with a range of 26dB is combined with two -20dB switched attenuators to provide levels down to 10mV pk-pk. Variable DC offset of \pm 10V is available via a centre detent control.

An auxilliary output provides a fixed 0 to +5V level suitable for driving both TTL and CMOS loads.

FREQUENCY

	FREQUENCT		
	Frequency Range:	0.2Hz to 20MHz in 8 overlapping decade ranges with fine adjustment by a vernier.	
	Vernier Range:	>10:1 on each range.	
	Vernier Accuracy:	Typically ±5% of full scale.	
SWEEP MODE (EXTERNAL)			
	Input Impedance:	82 kΩ	
	Sweep Range:	Typically $> 20:1$	
	Input Sensitivity: Max. Input Voltage:	Typically 0 to 2V for 10:1 sweep ±10V	
	Max. Slew Rate	±10V	
	of sweep voltage:	0.1V/us	
	OPERATING MODE	ES	
(Specifications apply for the top decade of each frequency range and output 10V peak-to- peak into 50Ω termination).			
	SINE		
	Distortion:	Typically 2% on 200, 2k and 20k ranges.	
	Amplitude Flatness:	± 0.2 dB to 200kHz; ± 2 dB to 200Hz.	
	TRIANGLE		
	Linearity:	Typically 99% on kHz ranges.	
	SQUAREWAVE		
	Rise and Fall Times:	<22ns	
	DC	<22115	
		40)///	
	Range:	$\pm 10V$ from 50 Ω	
	SYMMETRY	T : " : : : : : : : : : : : : : : : : :	
	Symmetry Range: OUTPUTS	Typically variable from 1:6 to 6:1 up to 500kHz.	
	50 Ω		
	Three switch-selectable ranges with 26dB vernier control within each		
	range.		
	0dB Range:	1V to 20V peak-to-peak (0.5V to 10V into 50 Ω).	
	-20dB Range:	100mV to 2V peak-to-peak (50mV to 1V into 50 Ω)	
	-40dB Range:	10mV to 0.2V peak-to-peak (5mV to 0.1V into 50	
	-	Ω)	
	DC Offset Range:	\pm 10V from 50 Ω. DC offset plus signal peak lim-	
		ited to $\pm 10V$ ($\pm 5V$ into 50 Ω). DC offset plus waveform attenuated proportionally in -20dB and	
		-40dB position.	
	TTL/CMOS	····	
Capable of driving 4 standard TTL loads.			
GENERAL			
	Power:	230V or 115V nominal 50/60Hz, adjustable inter-	
	r ower.	nally; operating range $\pm 14\%$ of nominal; 30VA	
		max. Installation Category II.	
	Operating Range:	+5°C to + 40°C, 20% to 80% RH.	
	Storage Range:	-10°C to +65°C	
	Environmental:	Indoor use at altitudes to 2000m, Pollution De-	
	Electrical Safety:	gree 1. Complies with EN61010-1.	
	Electrical Safety:		

Weight:

EMC:

Size:

Thurlby Thandar Instruments Ltd. operates a policy of continuous development and reserves the right to alter specifications without prior notice.

excluding feet.

1.5 Kg (3.3lb).

Complies with EN55011 and EN50082-1.

220(W) x 82(H) x 230(D) mm, (10.3 x 3.4 x 9.2")

Designed and built in the EEC by:



Thurlby Thandar Instruments Ltd. Glebe Road, Huntingdon. Cambs. PE29 7DR England Tel: +44 (0)1480 412451 Fax: +44 (0)1480 450409 e-mail: sales@tti-test.com Web: http://www.tti-test.com