



- Ensures the optimum alignment of reading head and code rail
- With prefitted mounting plate for reading head
- Cleaning brushes can be applied

WCS2-GT09-P1

Technical data

General specifications

Passage speed v ≤ 8 m/s

Ambient conditions

Operating temperature -40 ... 70 °C (-40 ... 158 °F)

Mechanical specifications

Bending radius ≥ 1000 mm

Material Metal sheet (steel), zinc-plated
Plastic rollers

Mass 1000 g

Dimensions

