

Double-ring wrench

Reinforced, open ring heads angled by 10°



Application:

Open double-end box wrench for e.g. hydraulic and brake lines.

Execution:

- Chrome-alloy steel
- Spanner width 8x10 to 12x14 mm - with hexagon profile
- Spanner width 14x17 to 30x32 mm – with bi-hexagon profile
- Spanner width 14x17 to 30x32 mm – with bi-hexagon profile

Advantage:

- Shaft profile creates excellent bending rigidity
- Can screw nuts onto pipes and rods, but with added benefits of a box wrench
- High force transmission to the edges of the bolts and nuts for optimum load distribution



Art. no.	52082 100
Brand	STAHLOWILLE
Manufacturer Part Number	41081922
Width across flats	19 x 22 mm
Length	230 mm
Tip profile type	AS drive profile
Surface	Chrome plated
Material	Steel, specially hardened
DIN	3118
Gross Weight	0.193 kg
Product Group	531

EAN

4018754021970