

Pneumatic air turbine grinder T 6-50 S

100 Watt



Application:

For fine deburring work in continuous use.

Execution:

- Rear air exhaust
- compact version
- Paired bearing

Advantage:

- Very long service life for fine work in continuous use thanks to larger paired bearing.
- Turbine motor - oil-free operation

Delivery:

Includes collet chuck ZG 4/6 mm, collet chuck key size 9 + 11 and hose unit; in box



Art. no.	75036 415
Brand	BIAX DRUCKLUFT
Manufacturer Part Number	150149820
Model	T 6-50 S
Valve design	Rotary valve
Motor design	Turbine motor
Max. idle speed	50000 rpm
Power output	100 W
Air consumption	270 l/min
Sound-pressure level	70 dB
Length	181 mm
Diameter of housing	30 mm
Max. clamping diameter	6 mm
Collet chuck diameter	6 mm
Suitable for max. sanding block diameter	10 mm
Max. HM rotating milling cutter diameter	6 mm
Weight	0.4 kg
Gross Weight	1.000 kg
Product Group	748