Zener Diode







Features

- · Planar Die construction
- 500mW Power Dissipation
- · Ideally Suited for Automated Assembly Processes

Mechanical Data

- Epoxy meets UL 94 V-0 flammability rating
- Moisture Sensitivity Level 1
- Approx. Weight: 0.009 grams

Maximum Ratings @ TA = 25°C unless otherwise specified

Characteristic	Symbol	Value	Unit
Max. Forward Voltage @ Ir = 10mA	VF	0.9	V
Junction Temperature (Note 1)	P(AV)	500	mW
Operating and Storage Temperature Range	TJ, TSTG	-55 to +150	°C

Note:

1. Mounted on 5mm² (0.013mm thick) land areas

Electrical Characteristics (TA = 25°C unless otherwise specified)

Part Number Marking		Normal Zener Voltage	Test Current	Max. Zener Impedance		Max. Reverse Leakage Current		Max. Zener Voltage
		Vz@lzt	lzt	Zzt@lzt@lzk=0.25mA		Ir@Vr		Temp.
		Volts	mA	Ω	Ω	μA	Volts	%/°C
MMSZ5232B+	E2	5.6	20	11	1600	5	3	+0.038
MMSZ5234B+	E4	6.2	20	7	1000	5	4	+0.045
MMSZ5236B+	F1	7.5	20	6	500	3	6	+0.058
MMSZ5237B+	F2	8.2	20	8	500	3	6.5	+0.062
MMSZ5242B+	H2	12	20	30	600	1	9.1	+0.077
MMSZ5248B+	J3	18	7	21	600	0.1	14	+0.085
MMSZ5252B+	K2	24	5.2	33	600	0.1	18	+0.088

Note:

- 1. Standard Zener voltage tolerance is ±5% with a "B" suffix (e.g.: MMSZ5225B)
- 2. Specials Available Include:
 - A. Nominal zener voltages between the voltages shown and tighter voltage tolerances.
 - B. Matched sets.
- 3. Zener Voltage (Vz) Measurement. Guarantees the zener voltage when measured at 90 seconds while maintaining the lead temperature (TL) at 30°C, from the diode body.
- 4. Zener Impedance (Zz) Derivation. The zener impedance is derived from the 60 cycle ac voltage, which results when an AC current having an rms value equal to 10% of the dc zener current (Izτ or Izκ) is superimposed on Izτ or Izκ.
- 5. Surge Current (IR) Non-Repetitive. The rating listed in the electrical characteristics table is maximum peak, non-repetitive, reverse surge current of 1/2 square wave or equivalent sine wave pulse of 1/120 second duration superimposed on the test current, IzT, per JEDEC registration.


Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro




Zener Diode



Rating and Characteristic Curves




NOMINAL ZENER VOLTAGE, Volts





Typical Reverse Current

Steady State Power Derating

Effect of Zener Voltage on Zener Impedance









Typical Forward Voltage


Steady State Power Derating

NOMINAL ZENER VOLTAGE, Volts

Typical Capacitance







Zener Voltage Vs. Zener Current

Zener Voltage Vs. Zener Current

Typical Leakage Current

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro




Zener Diode



Dimensions:

SOD-123



Dimensions					
Dim.	Inc	hes	mm		
	Min.	Max.	Min.	Max.	
Α	0.141	0.154	3.6	3.9	
В	0.098	0.11	2.5	2.8	
С	0.055	0.071	1.4	1.8	
D	0.037	0.053	0.95	1.35	
E	0.019	0.028	0.5	0.7	
F	-	0.008	-	0.2	
G	0.016	-	0.4	-	
Н	-	0.005	-	0.12	

Part Number Table

Description	Part Number
Zener Diode, 500mW 5.6V SOD-123	MMSZ5232B+
Zener Diode, 500mW 6.2V SOD-123	MMSZ5234B+
Zener Diode, 500mW 7.5V SOD-123	MMSZ5236B+
Zener Diode, 500mW 8.2V SOD-123	MMSZ5237B+
Zener Diode, 500mW 12V SOD-123	MMSZ5242B+
Zener Diode, 500mW 18V SOD-123	MMSZ5248B+
Zener Diode, 500mW 24V SOD-123	MMSZ5252B+

Important Notice: This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro

