




M4 THREAD
FOR LID SCREWS
4 PLACES



NOTES

DESIGNED TO MEET THE REQUIREMENTS OF IP65, & NEMA 4X
TONGUE & GROOVE CONSTRUCTION WITH A MOLDED ONE PIECE SILICON GASKET.
COMES WITH 4 STAINLESS STEEL MACHINE LID SCREWS, CAPTIVATED WITH 4 RUBBER O-RINGS.
COMES WITH 4 GROUNDING SCREWS AND WASHERS.
FINISH: NONE OR SUFFIX "BK" BLACK, OR SUFFIX "GY" GRAY (RAL 7001) POLYESTER POWDER



SIDE VIEWS DO NOT DETAIL
SCREW CHANNELS SEE
"A - A" FOR CHANNEL DETAIL

THIS DRAWING IS PROPRIETARY INFORMATION OF
HAMMOND MFG.CO.LTD. NOT TO BE USED WITHOUT
EXPRESSED WRITTEN PERMISSION
OF HAMMOND MFG.CO.LTD.

△	N/A	RELEASE	---	09/27/02	MJM
Rev.	ECN	Description		Date	By

Unless otherwise spec'd dimensions are in millimeters Tolerances are:		Dwn	M. MERCER
XX	±.25	Date	09/27/02
XXX	±.500	Chk	---
XXXX	±1.300	Mat'l	CAST ALUMINUM
Holes	±1.300	Sheet	1 of 1
Angles	±.5°	Part #	1590Z100

HAMMOND MANUFACTURING CO. LTD. Electronics Group, Waterloo, Ont. - Cheektowaga, NY	
HAMMOND 1590Z SERIES CASTED AL ENCLOSURES	
Dwg:	1590Z100/A

For the best fit print
on legal size paper.