# Product data sheet Characteristics

# XS518B1PAM12

inductive sensor XS5 M18 - L50mm - brass - Sn5mm - 12..24VDC - M12





#### Main

Range of product	OsiSense XS		
Series name	General purpose		
Sensor type	Inductive proximity sensor		
Device application	-		
Sensor name	XS5		
Sensor design	Cylindrical M18		
Size	50 mm		
Body type	Fixed		
Detector flush mounting acceptance	Flush mountable		
Material	Metal		
Type of output signal	Discrete		
Wiring technique	3-wire		
[Sn] nominal sensing distance	5 mm		
Discrete output function	1 NO		
Output circuit type	DC		
Discrete output type	PNP		
Electrical connection	Male connector M12 4 pins		
[Us] rated supply voltage	1224 V DC with reverse polarity protection		
Switching capacity in mA	<= 200 mA DC with overload and short-circuit protection		
degree of protection IP67 conforming to IEC 60529 IP69K conforming to DIN 40050			

### Complementary

o o mpromontary		
Thread type	M18 x 1	
Detection face	Frontal	-
Front material	PPS	i
Enclosure material	Nickel plated brass	

Operating zone	04 mm		
Differential travel	115% of Sr		
Status LED	1 LED (yellow) for output state		
Supply voltage limits	1036 V DC		
Switching frequency	<= 2000 Hz		
Voltage drop	<= 2 V, closed state		
Current consumption	<= 10 mA (no-load)		
Delay first up	<= 10 ms		
Delay response	<= 0.15 ms		
Delay recovery	<= 0.35 ms		
Marking	CE		
Threaded length	28 mm		
Height	18 mm		
Length	50 mm		

## Environment

Product certifications	CSA UL	
Ambient air temperature for operation	-2570 °C	
Ambient air temperature for storage	-4085 °C	
Vibration resistance	25 gn, amplitude: +/- 2 mm (f = 1055 Hz) conforming to IEC 60068-2-6	
Shock resistance	50 gn (duration = 11 ms) conforming to IEC 60068-2-27	

## Offer Sustainability


Sustainable offer status	Green Premium product  Compliant - since 0811 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity		Green Premium product	
RoHS (date code: YYWW)				
REACh	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold			
Product environmental profile	Available End of Life Information			
Product end of life instructions	Available			

## Contractual warranty

Warranty period	18 months	

# XS518B1PAM12

## **Dimensions**




# Product data sheet Mounting and Clearance

# XS518B1PAM12


## Minimum Mounting Distances

### Side by side




e (1) ≥ 10 mm/0.39 in.

Face to face



e (2) ≥ 60 mm/2.36 in. Facing a metal object



e (3) ≥ 15 mm/0.60 in

# Product data sheet Connections and Schema


# XS518B1PAM12

## Wiring Schemes

#### M12 connector



PNP




# Product data sheet **Performance Curves**

# XS518B1PAM12

### Performance Curves

## Standard Steel Target: 18x18x1 mm



- (1) (2) (y) Pick-up points
- Drop-out points (object approaching from the side)
- Sensing distance in mm