


DETAIL "A"
CHAMFER
SCALE=8:1

**UNCONTROLLED
DOCUMENT**

IMPEDANCE (Z)			
Frequency	25 MHz	100 MHz	300 MHz
Nominal (REF)	70 Ω	170 Ω	370 Ω
Minimum	- Ω	136 Ω	- Ω



FERRITE CORE DIMENSIONS (SPEC):mm[Inches]

A	25.00 [.984]	+ 0.50 [.020]
B	18.00 [.709]	+ 0.38 [.015]
C	16.00 [.630]	+ 0.32 [.013]
D	7.70 [.303]	+ 0.30 [.012]
E	0.90 [.035]	+ 0.20 [.008]

WEIGHT/1000 12.93 kgs [28.50 Lbs]

DIMENSIONS ARE IN mm [INCHES].				THIS DOCUMENT CONTAINS INFORMATION WHICH IS PROPRIETARY AND CONFIDENTIAL TO STEWARD. NO PRODUCTION OR PUBLICATION OF THIS DOCUMENT IN WHOLE OR IN PART SHALL BE MADE WITHOUT WRITTEN AUTHORIZATION FROM STEWARD.			
D	UPDATE MIN Z SPEC & COMPANY LOGO	07/27/07	JRK	DATE: 05/23/02	SCALE: 3:1	MATERIAL: NiZn FERRITE	
C	UPDATE MIN Z SPEC @100 Mhz, ADD REF #	01/26/04	JRK	CAD # 28R0984-200-D	TOOL # R0984		
B	UPDATE PRINT FORMAT AND Z SPECS	02/03/03	JRK				
A	ORIGINAL DRAFT	05/23/02	JRK				
REV	DESCRIPTION	DATE	INT				

SCALE DRAWING 1:1



28R0984-200