ON Semiconductor

Is Now



To learn more about onsemi™, please visit our website at www.onsemi.com

onsemi and ONSEMI. and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. onsemi reserves the right to make changes at any time to any products or information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/ or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi does not convey any license under any of its intellectual property rights nor the rights of others. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use onsemi products for any such unintended or unauthorized application,



ON Semiconductor®

FDN327N

N-Channel 1.8 Vgs Specified PowerTrench® MOSFET

General Description

This 20V N-Channel MOSFET uses ON Semiconductor's high voltage PowerTrench process. It has been optimized for power management applications.

Applications

- Load switch
- Battery protection
- Power management


Features


 $\bullet \ \ 2 \ A, \ 20 \ V. \qquad R_{DS(ON)} = 70 \ \ m\Omega \ @ \ V_{GS} = 4.5 \ V$

 $R_{\text{DS(ON)}} = 80 \ \text{m}\Omega \ @ \ V_{\text{GS}} = 2.5 \ \text{V}$

 $R_{DS(ON)}$ = 120 m Ω @ V_{GS} = 1.8 V

- Low gate charge (4.5 nC typical)
- · Fast switching speed
- High performance trench technology for extremely low R_{DS(ON)}





Absolute Maximum Ratings T_A=25°C unless otherwise noted

Symbol	Parameter		Ratings	Units	
V _{DSS}	Drain-Source Voltage		20	V	
V _{GSS}	Gate-Source Voltage		± 8	V	
I _D	Drain Current - Continuous	(Note 1a)	2	А	
	- Pulsed		8		
P _D	Power Dissipation for Single Operation	(Note 1a)	0.5	W	
		(Note 1b)	0.46		
T _J , T _{STG}	Operating and Storage Junction Temperature Range		-55 to +150	°C	

Thermal Characteristics

$R_{\theta JA}$	Thermal Resistance, Junction-to-Ambient	(Note 1a)	250	°C/W
$R_{\theta JC}$	Thermal Resistance, Junction-to-Case	(Note 1)	75	°C/W

Package Marking and Ordering Information

Device Marking	Device	Reel Size	Tape width	Quantity
327	FDN327N	7"	8mm	3000 units

Symbol	Parameter	Test Conditions	Min	Тур	Max	Units
Off Char	acteristics		·I	l	I	I
BV _{DSS}	Drain-Source Breakdown Voltage	$V_{GS} = 0 \text{ V}, \qquad I_{D} = 250 \mu\text{A}$	20			V
<u>ΔBV_{DSS}</u> ΔT _J	Breakdown Voltage Temperature Coefficient	I _D = 250 μA,Referenced to 25°C		12		mV/°C
I _{DSS}	Zero Gate Voltage Drain Current	$V_{DS} = 16 \text{ V}, \qquad V_{GS} = 0 \text{ V}$			1	μΑ
I _{GSSF}	Gate-Body Leakage, Forward	$V_{GS} = 8 \text{ V}, \qquad V_{DS} = 0 \text{ V}$			100	nA
I _{GSSR}	Gate-Body Leakage, Reverse	$V_{GS} = -8 \text{ V}, \qquad V_{DS} = 0 \text{ V}$			-100	nA
On Char	acteristics (Note 2)					
$V_{GS(th)}$	Gate Threshold Voltage	$V_{DS} = V_{GS}, I_{D} = 250 \mu A$	0.4	0.7	1.5	V
$\Delta V_{GS(th)} \over \Delta T_J$	Gate Threshold Voltage Temperature Coefficient	$I_D = 250 \mu A$, Referenced to $25^{\circ}C$		-3		mV/°C
$R_{DS(on)}$	Static Drain–Source On–Resistance	$\begin{tabular}{lllllllllllllllllllllllllllllllllll$		40 49 65 55	70 80 120 103	mΩ
I _{D(on)}	On-State Drain Current	$V_{GS} = 4.5V, V_{DS} = 5 V$	8			Α
g _{FS}	Forward Transconductance	$V_{DS} = 5V$, $I_{D} = 2 A$		11		S
Dynamic	Characteristics					
C _{iss}	Input Capacitance	$V_{DS} = 10 \text{ V}, \qquad V_{GS} = 0 \text{ V}$		423		pF
C _{oss}	Output Capacitance	f = 1.0 MHz		87		pF
C _{rss}	Reverse Transfer Capacitance	<u> </u>		48		pF
	g Characteristics (Note 2)			ı	I	I
t _{d(on)}	Turn-On Delay Time	$V_{DD} = 10 \text{ V}, \qquad I_{D} = 1 \text{ A},$		6	12	ns
t _r	Turn-On Rise Time	$V_{GS} = 4.5 \text{ V}, \qquad R_{GEN} = 6 \Omega$		6.5	13	ns
t _{d(off)}	Turn-Off Delay Time	- - -		14	29	ns
t _f	Turn-Off Fall Time			2	4	ns
Qg	Total Gate Charge	$V_{DS} = 10 \text{ V}, \qquad I_{D} = 2 \text{ A},$		4.5	6.3	nC
Q _{gs}	Gate-Source Charge	V _{GS} = 4.5 V		0.89		nC
Q_{gd}	Gate-Drain Charge	7		0.95		nC
Drain-Se	ource Diode Characteristics	and Maximum Ratings	•	•		•
Is	Maximum Continuous Drain–Source				0.42	Α
V _{SD}	Drain-Source Diode Forward Voltage	$V_{GS} = 0 \text{ V}, I_{S} = 0.42 \text{ A} \text{(Note 2)}$		0.6	1.2	V

Notes:

1. $R_{\theta JA}$ is the sum of the junction-to-case and case-to-ambient thermal resistance where the case thermal reference is defined as the solder mounting surface of the drain pins. $R_{\theta JC}$ is guaranteed by design while $R_{\theta CA}$ is determined by the user's board design.



a) 250°C/W when mounted on a 0.02 in² pad of 2 oz. copper.



b) 270°C/W when mounted on a minimum pad.

Scale 1:1 on letter size paper

2. Pulse Test: Pulse Width \leq 300 μ s, Duty Cycle \leq 2.0%

Typical Characteristics




Figure 1. On-Region Characteristics.




Figure 2. On-Resistance Variation with Drain Current and Gate Voltage.




Figure 3. On-Resistance Variation with Temperature.




Figure 4. On-Resistance Variation with Gate-to-Source Voltage.




Figure 5. Transfer Characteristics.





Figure 6. Body Diode Forward Voltage Variation with Source Current and Temperature.

Typical Characteristics







Figure 7. Gate Charge Characteristics.



Figure 8. Capacitance Characteristics.






Figure 9. Maximum Safe Operating Area.






Figure 11. Transient Thermal Response Curve.

Thermal characterization performed using the conditions described in Note 1b. Transient thermal response will change depending on the circuit board design.

ON Semiconductor and in are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and hol

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor 19521 E. 32nd Pkwy, Aurora, Colorado 80011 USA Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada Email: orderlit@onsemi.com N. American Technical Support: 800-282-9855 Toll Free USA/Canada Europe, Middle East and Africa Technical Support: Phone: 421 33 790 2910

Phone: 421 33 790 2910

Japan Customer Focus Center
Phone: 81–3–5817–1050

ON Semiconductor Website: www.onsemi.com

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative