

IEC Inlet with Fuse Holder


multicomp PRO



Specifications

Rating	: 10A / 250V AC
Withstand Voltage	: 2,000V AC for 1 minute
Insulation Resistance	: More than 100MΩ (at 500V DC)
Max. Operating Temperature	: -25°C to +85°C

Diagram



Item	Description	Material	Qty.	Finish	
1I	Body	Nylon 66, 94 V-2	1	-	
1J	Fuse Cover				
2B	Edge Terminal	Bsp1-1/2H, t = 2.0	2	Ni-plated	
3B	Centre Terminal				
4F	Connection Terminal	Bsp1-1/2H, t = 0.8	2	Sn-plated	
6C	Fuse Holder (Short)	Bsp1-1/2H, t = 0.5	1		
6B	Fuse Holder	Bsp1-1/2H, t = 0.8			
7A	Connector	Bsp1-1/2H, t = 0.6			Ni-plated
7B		Bsp1-1/2H, t = 0.4			Cu
7C					

Part Number Table

Description	Part Number
IEC Inlet with Fuse Holder, 10A/250V AC	JR-101-1-FRSG-03

Dimensions : Millimetres

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro
 Farnell.com/multicomp-pro
 sg.element14.com/b/multicomp-pro

multicomp PRO