

Vertical clamp

Heavy-duty



Application:

For quick clamping of workpieces.

Version:

- With horizontal base
- Reamed and case-hardened bearing bushes
- Hardened, polished and permanently lubricated studs
- burnished steel, lever arm made of steel casting
- With red oil-resistant plastic handle

Delivery:

With tempered and galvanised thrust bolt



Art. no.	26212 520
Size	2
Hole distance	32 mm
Bore diameter	7.1 mm
Clamping height	25 mm
Retaining force	2.5 kN
Length, clamped	85 mm
Length, open	94 mm
Thumbscrew size	M6 x 50 mm

EAN-Code

4020772091316