

ROOF MOUNTED FAN AIR FLOW FREE AIR 405 M3  
 PER H CUT OUT 345X265 MM 115 V AC RAL7035  
 INPUT POWER 40W DEGREE OF PROTECTION IP 44



Figure similar

Model		
product brand name		SIVACON
Product designation		Roof fans
Type of ventilation		ventilation
Fan design / Insertable fan		No
Design of the product / EMC version		No
General technical data		
A-rated sound power level / maximum	dB	62
Active power consumption / Rated value	W	40
Cutout width	mm	345
Cutout height	mm	265
Operating period	h	40 000
Operating temperature / minimum	°C	-10
Rotor speed / at 50 Hz / Rated value	1/min	1 430
Rotor speed / at 60 Hz / Rated value	1/min	1 700
Protection class		
Protection class IP		IP54
Electricity		
Consumed current / minimum	A	0.35
Main circuit		
Operating voltage		
• with AC / at 50 Hz / Rated value / maximum	V	115
• with AC / at 60 Hz / Rated value / maximum	V	115

## Appearance

**Color** RAL 7035

## Product details

**Product component / Fan** Yes

## Number

**Number of ventilators** 1

## Mechanical Design

**Height** mm 340

**Width** mm 420

**Depth** mm 108

**Installation location** Control cabinet roof

**Mounting type** screw fixing

### Mounting type

- 19-inch installation No
- wall mounting No

**Material** plastic

## Certificates

### Equipment marking

- acc. to DIN EN 61346-2 E
- acc. to DIN EN 81346-2 E

## General Product Approval



## Further information

### Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

### Industry Mall (Online ordering system)

<https://eb.automation.siemens.com/mall/en/WW/Catalog/Product/8MR63115DL40>

### Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<http://support.automation.siemens.com/WW/view/en/8MR63115DL40/all>

### Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mfb=8MR63115DL40](http://www.automation.siemens.com/bilddb/cax_en.aspx?mfb=8MR63115DL40)

### CAX-Online-Generator

<http://www.siemens.com/cax>

### Tender specifications

<http://ausschreibungstexte.siemens.com/tiplv>

**last modified:** 11.03.2015