

Für Feinarbeiten an weichbleibenden Unterfütterungsmaterialien (91RF-95RF)

For finishing permanent soft relining material (91RF-95RF)

Para alisar materiales de rebase permanentemente blandos (91RF-95RF)

91RF stainless steel



Fig.	Shank	ISO-No.		5
91RF	HP	330 104 001 132		050



92RF stainless steel



Fig.	Shank	ISO-No.		5
92RF	HP	330 104 155 132	L mm	10,0
				050



95RF stainless steel




Fig.	Shank	ISO-No.		5	5	5	5
95RF	HP	330 104 260 132	L mm	9,5	11,0	12,5	14,0
				040	050	060	070



I04RF stainless steel



Fig.	Shank	ISO-No.		1
I04RF	HP	330 104 099 172	L mm	3,5
				100



108 steel




Fig.	Shank	ISO-No.		2
108	HP	310 104 118 174	L mm	3,7
				060



Reparaturfräser

Groove cutter for repairs

Fresa para cortar ranuras para reparaciones

231 steel




Fig.	Shank	ISO-No.		10	5	5	5
231	HP	310 104 045 171	L mm	0,2	0,3	0,4	0,5
				023	040	060	100



Kreissäge

Circular saw

Sierra circular

232RF stainless steel




Fig.	Shank	ISO-No.		10	10	10	10	10
232RF	unmounted	330 900 320 101	L mm	0,1	0,1	0,1	0,1	0,1
				125	160	190	220	250



Kreissäge, rostfrei

Circular saw, stainless

Sierra circular, inoxidable