



35W CONVECTION COOLED

The LCS series of regulated output convection cooled AC-DC power supplies are designed to provide a cost effective solution for industrial electronics and technology applications. Features include output voltage adjustment, a power 'ON' LED, low stand-by power consumption, output short circuit protection, over current and over voltage protection. Applications include auxiliary power sources, security installations, lighting control, smart home or office control systems, ticketing and vending applications.

Features

- 35W convection cooled
- ITE & industrial approvals
- Integrated connector cover
- Class B conducted & radiated emissions
- Input voltage range 85-264VAC
- 300VAC withstand voltage for 5s
- Output voltages from 5V to 24VDC
- Efficiency to 88%
- Short circuit, overvoltage & overload protection
- Conformal coating option
- -30°C to +70°C operating temperature
- 3 year warranty

AC-DC POWER SUPPLIES



Applications





Industrial Electronics

Technology

Dimensions

3.89" x 3.23" x 1.18" (99.0 x 82.0 x 30.0 mm)

Models & Ratings

| Model Number(3) | Output Voltage | | Output Voltage Ripple & Output Current | Ripple & Noise | Efficiency ⁽²⁾ | Maximum | Power |
|-----------------|----------------|---------------------------------|--|-------------------------|---------------------------|-----------------|-------|
| Model Nulliber | Nominal | Adjustment Range ⁽⁴⁾ | Output Current | pk to pk ⁽¹⁾ | Efficiency | Capacitive Load | rowei |
| LCS35US05 | 5.0V | 4.5 - 5.5V | 7.0A | 80mV | 82% | 8000μF | 35W |
| LCS35US12 | 12.0V | 10.2 - 13.8V | 3.0A | 120mV | 86% | 1500µF | 36W |
| LCS35US15 | 15.0V | 13.5 - 18.0V | 2.4A | 120mV | 88% | 1000μF | 36W |
| LCS35US24 | 24.0V | 21.6 - 28.8V | 1.5A | 180mV | 88% | 750µF | 36W |

Notes:

- $1. \ \text{Ripple \& noise measured with 20MHz bandwidth and 47} \\ \mu F \ \text{electrolytic capacitor in parallel with 0.1} \\ \mu F \ \text{ceramic capacitor.}$
- 2. Typical efficiencies measured at 230VAC full load.
- $3. \, Add \, suffix \, \hbox{-E to model number to specify conformal coating option, MOQ applies, please contact sales.} \\$
- 4. Output power rating must not be exceeded.

─ LCS35 Series

Input

| Characteristic | Minimum | Typical | Maximum | Units | Notes & Conditions |
|---------------------------|---|---------|---------|-------|--|
| | 85 | 115/230 | 264 | VAC | Derate output power linearly from 100% at 100VAC to 80% at 85VAC |
| Input Voltage - Operating | 120 | | 373 | VDC | Alternative input. Not to be used in addition to AC input. DC input not included in safety approvals, external DC rated fuse required. Derate output power linearly from 100% at 140VDC to 80% at 120VDC |
| Input Frequency | 47 | 50/60 | 63 | Hz | |
| Surge Withstand | 300VAC for maximum 5s | | | | |
| Innut Cument Full Load | | 0.8 | | ^ | 115VAC |
| Input Current - Full Load | | 0.6 | | А | 230VAC |
| No Load Input Power | | | 0.3 | W | |
| Inwork Comment | | 30 | | ٨ | 115VAC cold start at 25°C ambient |
| Inrush Current | | 50 | | А | 230VAC cold start at 25°C ambient |
| Earth Leakage Current | | | 0.75 | mA | 230VAC/50Hz (Typ) |
| Input Protection | T2A / 250VAC Internal fuse fitted in line | | | | |

Output

| Characteristic | Minimum | Typical | Maximum | Units | Notes & Conditions | | ions | |
|--------------------------|---------|---------|---------|-------------|--|---------------------------------------|--|--|
| Output Voltage | 5 | | 24 | VDC | See Mode | ls & R | atings table | |
| Initial Set Accuracy | | ±2 | | % Full load | | LC | S35US05 | |
| | | ±1 | | | LC | S35US12, LCS35US15, LCS35US24 | | |
| Voltage Adjustment | | | ±10 | % | | | | |
| Minimum Load | 0 | | | А | No minimum load required | | | |
| Start Up Delay | | | 300 | ms | 115/230VAC full load | | load | |
| Held He Time | | 8 | | | 115VAC | | | |
| Hold Up Time | | 30 | | ms | 230VAC | | | |
| Drift | | | ±0.03 | % | After 20 minutes warm up, 230VAC, 0°C to 50°C | | s warm up, 230VAC, 0°C to 50°C | |
| Line Regulation | | | ±0.5 | % | 100-264VA | AC, ful | II load | |
| Load Regulation | | | ±1 | % | 0-100% LCS35US05 | | S35US05 | |
| | | | ±0.5 | | load | LC | S35US12, LCS35US15, LCS35US24 | |
| Transient Response | | | 10 | % | Recovery within 1% in less than 3ms for a 50-75% and 75-50% step | | 1% in less than 3ms for a 50-75% and 75-50% load | |
| | | 80 | | | LCS35US | 05 | | |
| | | 120 | | mV | LCS35US | 12 | 20MHz bandwidth and 47μF electrolytic capacito | |
| Ripple & Noise | | 120 | | pk-pk | LCS35US | 15 | parallel with 0.1µF ceramic capacitor | |
| | | 180 | | | LCS35US2 | 24 | | |
| Over/Undershoot | | | 10 | % | Full load | | | |
| | | | 6.3 | | LCS35US | 05 | | |
| | | | 16.2 | | LCS35US | 12 | | |
| Overvoltage Protection | | | 21.75 | VDC | LCS35US | 15 | Auto recovery | |
| | | | 33.6 | | LCS35US2 | 24 | | |
| Overload Protection | 110 | | 200 | % | Nominal o | Nominal output current, auto recovery | | |
| Temperature Coefficient | | ±0.03 | | %/°C | | - | · | |
| Short Circuit Protection | | | 5 | s | Trip and restart, auto recovery | | auto recovery | |

─ LCS35 Series

General

| Characteristic | Minimum | Typical | Maximum | Units | Notes & Conditions |
|----------------------------|--|-------------|---------|-------|---|
| Efficiency | | 86 | | % | 230VAC Full load (see Models & Ratings table) |
| Isolation: Input to Output | 4000 | | | VAC | |
| Input to Ground | 2000 | | | VAC | Class I construction |
| Output to Ground | 1250 | | | VAC | |
| Switching Frequency | | 65 | | kHz | |
| Power Density | | | 2.36 | W/in³ | |
| Mean Time Between Failure | 300 | | | khrs | MIL-HDBK-217F, Notice 2 +25°C GB |
| Weight | | 0.396 (180) | | lb(g) | |
| Case Material | Aluminium chassis with vented galvanized steel cover | | | | |
| Conformal Coating Option | on Acrylic resin, UL94V-0 rated, certified (UL No. E351072), minimum 30µm coating thickness. Add suffix -E to pa | | | | m coating thickness. Add suffix -E to part number |

Environmental

| Characteristic | Minimum | Typical | Maximum | Units | Notes & Conditions | |
|-----------------------|---|--------------------|---------|-------|--------------------|--|
| Operating Temperature | -30 | | +70 | °C | See derating curve | |
| Storage Temperature | -40 | | +85 | °C | | |
| Cooling | Natural convection | Natural convection | | | | |
| Humidity | 5 | | 90 | %RH | Non-condensing | |
| Operating Altitude | | | 5000 | m | | |
| Shock and Vibration | Tested according to EN60068-2-27, 10 - 500Hz, 5g (1H) for each X, Y and Z plane | | | | | |

EMC: Emissions

| Phenomenon | Standard | Test Level | Notes & Conditions |
|------------------|-------------|------------|--------------------|
| Conducted | EN55032 | Class B | |
| Radiated | EN55032 | Class B | |
| Harmonic Current | EN61000-3-2 | Class A | |

EMC: Immunity

| Phenomenon | Standard | Test Level | Criteria | Notes & Conditions |
|-------------------|--------------|--|----------|--|
| ESD Immunity | EN61000-4-2 | 3 | Α | Contact ±6kV / Air ±8kV |
| Radiated Immunity | EN61000-4-3 | 3 | А | 10V/m |
| EFT | EN61000-4-4 | 3 | А | ±2kV |
| Surge | EN61000-4-5 | Installation class 4 | А | Line to line ±2kV, line to ground ±4kV |
| Conducted | EN61000-4-6 | 3 | А | 10Vrms |
| Dips | EN61000-4-11 | Dip. 100% (0VAC), 10ms Dip. 100% (0VAC), 20ms Dip. 60% (88VAC), 200ms Dip. 30% (154VAC), 500ms Dip. 20% (176VAC), 5000ms | А | |
| Interrupt | | Int. 100% (0VAC), 5000ms | В | |




Safety Approvals

| Safety Agency | Standard | Notes & Conditions |
|---------------|-----------|------------------------|
| UL | UL62368-1 | Information Technology |
| TUV | EN62368-1 | Information Technology |
| CE | LVD | |

Application Notes


Temperature Derating




Notes:

- 1. With 230VAC or 140VDC input no derating below -25°C
- 2. With input at 100VAC or 120VDC derate output power to 75%

Mechanical Details





| Pin-Out | | | |
|---------|----------|--|--|
| Pin | Function | | |
| 1 | AC(L) | | |
| 2 | AC(N) | | |
| 3 | | | |
| 4 | -Vo | | |
| 5 +Vo | | | |

Connector torque: M3.5, 0.8Nm

Notes:

- 1. All dimensions are in inches (mm).
- 2. Tightening torque: M3, 0.4Nm fixings
- 3. General tolerances: ±0.039 (±1.00)
- 4. Chassis must be connected to protective earth.