




A RANGE OF HIGH QUALITY PHONO PLUGS MADE FROM MACHINED BRASS WITH VARIOUS PLATING OPTIONS

- CENTRE CONTACT, SOLID PIN
- GROUND CONTACT WITH 'T' SHAPE SLOT FOR MAXIMUM CONTACT AREA
- SPRING STRAIN RELIEF
- COLOUR CODE ID RINGS AVAILABLE IN RED AND BLACK



MATERIAL PROPERTIES

PART	MATERIAL	FINISH
CENTRE CONTACT	BRASS	SILVER OR FLASH GOLD
GROUND CONTACT	BRASS	NICKEL OR FLASH GOLD
INSULATION	NORYL SE1	
CABLE CLAMP	BRASS	SILVER OR FLASH GOLD
SPRING	SPRING STEEL	NICKEL, FLASH GOLD OR BLACK PLATED
CAP	BRASS	NICKEL, FLASH GOLD OR BLACK PLATED
ID RING	ACETAL	RED OR BLACK

ELECTRICAL PROPERTIES

RATED CURRENT		5A
RATED VOLTAGE		50 V
INSULATION RESISTANCE		100M W at 500 VDC
MAXIMUM CABLE SIZE		5.5mm

TEMPERATURE PROPERTIES

ACETAL, DELRIN, 500P BK602	ID RING	RTI 105°C CTI 600V, UL94-HB CLTE -40°C to 23°C 9.0E-5cm/cm°C
NORYL RESIN SE1		RTI 110°C CTI 400V, UL95-V1 CLTE -40°C to 40°C 8.0E-5cm/cm°C

PART NUMBERS

PART No	FINISH	COLOUR ID
333-0000	NICKEL PLATED	NONE
333-0100	NICKEL PLATED	BLACK
333-0500	NICKEL PLATED	RED
334-0000	FLASH GOLD PLATED	NONE
334-0100	FLASH GOLD PLATED	BLACK
334-0500	FLASH GOLD PLATED	RED
335-0000	FLASH GOLD PLUG / BLACK CAP	NONE
335-0100	FLASH GOLD PLUG / BLACK CAP	BLACK
335-0500	FLASH GOLD PLUG / BLACK CAP	RED