

U.I. Lapp GmbH	PRODUCT INFORMATION	
	SKINTOP® KR-M ATEX plus blue	07.11.2014

For the benefits, refer to SKINTOP® K-M ATEX plus blue



Mechanical resistance



Oil & Gas



Optimum strain relief



Reliability



Variety of approval certifications

Application range

With reducing seal insert, to seal cables with smaller outer diameters.

Product Make-up

Metric connection thread acc. to EN 50262

Remark

Photographs are not to scale and do not represent detailed images of the respective products.

Technical Data

Caution:	Refer to the instruction leaflet for the installation dimensions and torques
Approvals:	CE 0637 Ex II 2G Ex eb IIC Ex II 1D Ex ta IIIC IECEx IBE 13.0027X
Classification:	ETIM 5.0 Class-ID: EC000441 ETIM 5.0 Class-Description: cable screw gland
Colour delivered:	Blue (RAL 5015)
Material:	Body: special polyamide Seal: special elastomer O-ring: CR
Tests:	DIN EN 60079-0 DIN EN 60079-7
Protection rating:	IP 68 - 10 bar
Temperature range:	-20°C to +80°C


Product Management	Document: LAPP_PRO985EN.pdf	1 / 3
--------------------	-----------------------------	-------

SKINTOP® KR-M ATEX plus blue

07.11.2014

Part number	Article designation / size	Clamping range ØF (mm)	Thread M	SW (mm)	Overall length/ C (mm)	Thread length/ D (mm)	Pieces / PU
SKINTOP® KR-M ATEX plus blue							
54115405	KR-M 12 ATEX plus blue	2-4	12 x 1.5	15	26,5 - 30	8.0	50
54115415	KR-M 16 ATEX plus blue	4-6	16 x 1.5	19	29 - 34	8.0	50
54115425	KR-M 20 ATEX plus blue	5-10	20 x 1.5	25	34 - 37	9.0	50
54115435	KR-M 25 ATEX plus blue	6-13	25 x 1.5	30	35 - 40	10.0	25
54115445	KR-M 32 ATEX plus blue	9-15	32 x 1.5	36	39 - 47	10.0	25
54115455	KR-M 40 ATEX plus blue	16-23	40 x 1.5	46	43 - 52	10.0	10
54115465	KR-M 50 ATEX plus blue	22-29	50 x 1.5	55	54 - 62	12.0	5
54115475	KR-M 63 ATEX plus blue	29-39	63 x 1.5	66	59 - 71	12.0	5

U.I. Lapp GmbH	PRODUCT INFORMATION	
	SKINTOP® KR-M ATEX plus blue	07.11.2014



Product Management	Document: LAPP_PRO985EN.pdf	3 / 3
--------------------	-----------------------------	-------