

Multi-purpose cabinet with clothes rail and shelves

With partition, height 1950 mm

Application:

For secure and clearly-arranged storage of clothing, tools, accessories and other parts.

Version:

- Stable welded steel sheet structure with base
- Interior fittings: 5 shelves on the left, 1 shelf on the right above 1 clothes rail with 3 sliding hooks
- Shelves, powder-coated, height-adjustable in increments of 17 mm
- Inset-type doors with internal pivot pins, doors reinforced by box profile on inside, approx. 125° door opening angle
- Locks by means of turning handle with triple-point security cylinder lock, incl. 2 keys

Delivery:

DOM locking system (suitable for HK tool cabinets, HK tool shelves, HK workbenches, HK hinged-door and sliding door cabinets) and other colours deliverable upon request.



Art. no.	50108 053
Door design	Full-sheet panel
Width	1000 mm
Depth	500 mm
Height	1950 mm
Number of shelves	6 PCS
Load-carrying capacity per shelf	30 kg
Load-carrying capacity	400 kg
With partition wall	Yes
Central locking	Yes
Lock type	Twist-grip lock with three-point fastening
Material	Sheet steel
Cabinet colour	Light grey RAL 7035
Colour of front	Gentian blue RAL 5010
Surface	Powder-coated