

Cabinet workbench series V 1500 with lowerable transport wheels

Zinc sheet coating 1500 mm, 4 drawers with full extension, lever-operated wheels



Execution:

- Solidly welded steel sheet construction
- Base made of square-section steel tube 45 x 45 x 2 mm, with level compensation
- 2 drawers with 100% full extension on the left and right, 1 x front height 180 mm, 1 x front height 360 mm



Art. no.	50201 530
Brand	ANKE
Manufacturer Part Number	999.001.1209
Working height	850 mm
Worktop width	1500 mm
Number of drawers	4 PCS
Worktop height	50 mm
Worktop depth	700 mm
Pullout type	Full extension
On castors	Yes
Colour of front	Optional
Cabinet colour	Optional
Drawer surface	0.27 m ²
With single pull-out safety brake	Yes
Surface	Powder-coated
Load-carrying capacity	450 kg
Levelling	Yes
Lock type	DOM® locking system
Material of worktop	Zinc sheet covering
Drawer front height	2 x 180 mm, 2 x 360 mm
Drawer width (inner dimension)	500 mm
Drawer width (inner dimension) x drawer depth (inner dimension)	500 x 540 mm
Drawer depth (inner dimension)	540 mm
Load-carrying capacity per drawer	100 kg
Central locking	Yes
Gross Weight	170.052 kg
Product Group	502

EAN

4014641070199