

## Tool cabinet with shelves

Doors optionally with perforated panel, slotted panel or viewing window

<sup>®</sup>RasterPlan

### Application:

For secure and clearly-arranged storage of high-quality tools.

### Execution:

- Welded sheet steel frame with perforated rear wall throughout with 10 x 10 mm perforation grid, for attaching support elements
- Overlay double-walled, twist-resistant hinged doors, opening angle over 200°
- Doors lockable with bascule lock engaging on 3 sides



<b>Art. no.</b>	<b>50639 118</b>
<b>Brand</b>	RASTERPLAN
<b>Manufacturer Part Number</b>	1352.01.4016
<b>Door design</b>	Slotted plates
<b>Width</b>	1000 mm
<b>Depth</b>	410 mm
<b>Height</b>	1950 mm
<b>Number of shelves</b>	2 PCS
<b>Shelf width</b>	1000 mm
<b>Shelf depth</b>	410 mm
<b>Load-carrying capacity per shelf</b>	80 kg
<b>With partition wall</b>	No
<b>Central locking</b>	Yes
<b>Lock type</b>	Twist-grip lock with three-point fastening
<b>Material</b>	Sheet steel
<b>Colour of front</b>	Gentian blue RAL 5010
<b>Surface</b>	Lacquered
<b>Cabinet colour</b>	Light grey RAL 7035
<b>Gross Weight</b>	75.800 kg
<b>Product Group</b>	5AC

### EAN

4251142216507