

## Magnetic welding bracket 90°, fixed

### Application:

for firmly securing sheet metal, panels, flat and angular steel parts, profiles.

### Execution:

- No deflection of the light arc
- ref. no. 120 For holding round parts such as pipes and bars

<b>Art. no.</b>	<b>51129 100</b>
<b>Width of side</b>	38 mm
<b>Limb length</b>	115/105 mm
<b>Angle</b>	90 Degree
<b>Gross Weight</b>	0.670 kg
<b>Product Group</b>	592

