

## Cordless screw tap GB 18 LTX Q I device only

Full-fledged cordless drill screwdriver with unique, patented thread cutting function

**metabo**

### Execution:

- With two quick-change screw tap chucks for accommodating screw taps with square and cylindrical drill bits
- Metabo Quick system: Fast changing of tool chuck and plug-in tool for flexible working
- Impulse mode function for unscrewing seized screws and spot-drilling on smooth surfaces
- Precision Stop: electronic torque coupling with increased precision for accurate and sensitive work
- Overload protection: protects the motor from overheating

### Advantage:

- Fast and interruption-free drilling and cleaning of threads by automatic switching of the direction of rotation
- The screw taps have long service life thanks to intelligent torque monitoring
- Electronic safety cut-off: no kick-back if the drill jams – for excellent user protection

### Delivery:

Does not include battery or charger; incl. quick-change screw tap chuck M4–M6 and M8–M12, additional handle, belt hook and bit depot



<b>Art. no.</b>	<b>71037 899</b>
<b>Model</b>	GB 18 LTX Q I
<b>Motor design</b>	Brushless motor
<b>Number of rechargeable batteries/batteries</b>	0
<b>Max. drilling diameter in wood</b>	65 mm
<b>Max. drilling diameter in steel</b>	13 mm
<b>Max. thread-cutting performance</b>	M12
<b>Min. thread-cutting performance</b>	M4
<b>Idle speed 1st gear min./max.</b>	0-500 rpm
<b>Max. torque hard/soft</b>	130 / 65 Nm
<b>Idle speed 2nd gear min./max.</b>	0-2000 rpm
<b>Min./max. drill chuck span width</b>	1.5-13 mm
<b>Battery included</b>	No
<b>With working lights</b>	No
<b>With rubber-coated handle</b>	Yes
<b>With quick clamping system</b>	Yes
<b>With overload protection</b>	Yes
<b>With impulse function</b>	Yes
<b>With battery capacity display</b>	No
<b>Tool holding device</b>	Metabo Quick
<b>Min./max. torque adjustment</b>	1-20 Nm
<b>Product Group</b>	Prod. Gr. 745

### EAN

4061792188198