









Model Number

RC10-14-N3

Features

- 10 mm inside diameter
- **Bistable**
- **Direction detection**

Technical Data		
General specifications		
Switching element function		NAMUR, bistable
Installation		
Output polarity		NAMUR
Inside diameter		10 mm
Measuring cylinder		
Diameter		2.5 mm
Length		3 mm
Measuring cone		
Material		9S20K
Nominal ratings		
Nominal voltage	U	8.2 V (R_i approx. 1 k Ω)
Hysteresis	H	typ. 1 %
Reverse polarity protection		reverse polarity protected
Current consumption		
Traverse B		3 mA
Traverse A		1 mA
Time delay before availability	t _v	≤5 ms
Functional safety related param	eters	
MTTF _d		2144 a
Mission Time (T _M)		20 a
Diagnostic Coverage (DC)		0 %
Ambient conditions		
Ambient temperature		-20 100 °C (-4 212 °F)
Mechanical specifications		
Connection type		cable PVC , 2 m
Core cross-section		0.14 mm ²
Housing material		PBT
Degree of protection		IP67
General information		
Use in the hazardous area		see instruction manuals
Category		2G
Compliance with standards and	directive	es
Standard conformity		
NAMUR		EN 60947-5-6:2000
-		IEC 60947-5-6:1999
Standards		EN 60947-5-2:2007


IEC 60947-5-2:2007

Approvals and certificates


FM approval

Control drawing 116-0165F cULus Listed, General Purpose UL approval CSA approval cCSAus Listed, General Purpose

Dimensions



Electrical Connection



ATEX 2G

Instruction

Device category 2G

EC-Type Examination Certificate CE marking

ATEX marking

Directive conformity

Standards

Appropriate type

Effective internal capacitance C_i Effective internal inductance L_i

General

Ambient temperature

Installation, Comissioning

Maintenance

Specific conditions

Manual electrical apparatus for hazardous areas

for use in hazardous areas with gas, vapour and mist PTB 99 ATEX 2128 X

€0102

⟨ II 2G Ex ia IIC T6 Gb

94/9/FG

EN 60079-0:2009, EN 60079-11:2012 Ignition protection "Intrinsic safety"

Use is restricted to the following stated conditions

RC10-...-N3..

 \leq 90 nF; a cable length of 10 m is considered.

 \leq 120 μH ; a cable length of 10 m is considered.

The apparatus has to be operated according to the appropriate data in the data sheet and in this instruction manual. The EC-Type Examination Certificate has to be observed. The special conditions must be adhered to!

The temperature ranges, according to temperature class, are given in the EC-Type Examination Certificate.

Laws and/or regulations and standards governing the use or intended usage goal must be observed. The intrinsic safety is only assured in connection with an appropriate related apparatus and according to the proof of intrinsic safety.

No changes can be made to apparatus, which are operated in hazardous areas. Repairs to these apparatus are not possible.

